


HSS-HF 1 17.0-23.0/50Y**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

| | |
|------------|------------------------------------------------------------------------------------|
| Version | Conductor markers, Conductor and cable markers, 17 - 23 mm, 50.8 x 42.2 mm, yellow |
| Order No. | 1961960000 |
| Type | HSS-HF 1 17.0-23.0/50Y |
| GTIN (EAN) | 4032248642656 |
| Qty. | 750 items |

HSS-HF 1 17.0-23.0/50Y

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 0.77 mm | Depth (inches) | 0.0303 inch |
| Height | 50.8 mm | Height (inches) | 2 inch |
| Width | 42.2 mm | Width (inches) | 1.6614 inch |
| Net weight | 3.34 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -55...105 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|----------------------------------------------|-------------------------------------------------------------------------------|-----------------------------------|----------------|
| Material colour according to resistance code | 4 | Type of printing | neutral |
| Width | 42.2 mm | Operating temperature range, max. | 105 °C |
| Operating temperature range, min. | -55 °C | Colour | yellow |
| Halogen | No | Basic material | Polyolefine |
| Printed characters compatible printer | without THM MULTIMARK , THM MULTIMARK PLUS | Recommended industries | Transportation |
| | | Operating temperature range | -55...105 °C |

Conductor and cable markers

| | | | |
|-----------------------------------|--------------------------|-------------------------------|---------------------|
| Halogen | No | Conductor cross-section, max. | 120 mm ² |
| Conductor cross-section, min. | 70 mm ² | Conductor O.D., max. | 23 mm |
| Conductor O.D., min. | 17 mm | Rate of shrinkage | 2:1 |
| Recommended shrinking temperature | 90 °C | Text field width | 50.8 mm |
| Text field height | 40.6 mm | Conductor O.D. | 17 - 23 mm |
| Cross-section for connected wire | 70 - 120 mm ² | | |

Classifications


| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

HSS-HF 1 17.0-23.0/50Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



Bestellhilfe

HSS-HF 1/8" 1,2-2,8 / 50 Y

- Y = Gelb (W=Weiß)
- 50,8 mm Hüslenlänge (oder 25,4 mm)
- geeigneter Leiterdurchmesser 1,2 - 2,8mm
- Max. Außendurchmesser 1/8" (bzw. 3,2 mm)
- HF = Halogenfrei nach VDE 0472-615
- HSS = Heat Shrinkable Sleeve (wärmeschrumpfender Schlauch)

HSS-HF 1 17.0-23.0/50Y

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|------------|--|
| Type | RIBBON MM-HS 60/300 SW | Version | |
| Order No. | 2448880000 | Ink ribbon | |
| GTIN (EAN) | 4050118462944 | | |
| Qty. | 1 ST | | |

THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | MULTIMARK ROLLER 115 | Version | |
| Order No. | 1357420000 | | |
| GTIN (EAN) | 4050118160314 | | |
| Qty. | 1 ST | | |

THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | MULTIMARK PLUS ROLLER 1... | Version | |
| Order No. | 2672590000 | | |
| GTIN (EAN) | 4050118708097 | | |
| Qty. | 1 ST | | |