

IE-BS-V04P-SCRJ2SC-MM-C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



PushPull plug-in connector set according to IEC
61076-3-106 ver.4 (IEC24702), plastic with SC insert

General ordering data

| | |
|------------|--|
| Version | Flange FO, IP67, Version 4, coupling from SCRJ on 2*SC, Multimode, POF |
| Order No. | 1964470000 |
| Type | IE-BS-V04P-SCRJ2SC-MM-C |
| GTIN (EAN) | 4032248649075 |
| Qty. | 10 items |

IE-BS-V04P-SCRJ2SC-MM-C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 48.3 mm | Depth (inches) | 1.9016 inch |
| Height | 38 mm | Height (inches) | 1.4961 inch |
| Width | 27 mm | Width (inches) | 1.063 inch |
| Net weight | 3.25 g | | |

Temperatures

| | | |
|--------------------------|-----------------------|----------------|
| Storage temperature | Operating temperature | -40 °C...70 °C |
| Installation temperature | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|------------------------|---------------------------------------|---------------------------|----------------|
| Description of article | Version 4, coupling from SCRJ on 2*SC | Colour | Miscellaneous |
| Housing main material | PA UL 94 V0 | Protection degree | IP67 |
| Plugging cycles | 500 | Fibre type | Multimode, POF |
| Insertion loss | ≤ 0.4 dB | Connection 1 | SC |
| Connection 2 | SCRJ | Return loss (attenuation) | ≥ 30 dB |


General standards

| | |
|--------------------|---|
| Connector standard | IEC 61076-3-106 Var. 4, IEC 61754-4, IEC 61754-24 |
|--------------------|---|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000752 | ETIM 9.0 | EC000752 |
| ETIM 10.0 | EC000752 | ECLASS 14.0 | 19-17-01-16 |
| ECLASS 15.0 | 19-17-01-16 | | |

Installation cut-out



Mounting cut-out: 1. With central screw connection / 2. For mounting with four M3 screws

IE-BS-V04P-SCRJ2SC-MM-C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Dust caps




For protecting your devices against dust and dirt.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | IE-BP-V04P | Version | |
| Order No. | 1963900000 | Flange-mounted housing, protective cap | |
| GTIN (EAN) | 4032248646326 | | |
| Qty. | 10 ST | | |

Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | ESG 9/11 K MC NE WS | Version | |
| Order No. | 1857440000 | ESG, Device markers x 11 mm, PA 66, Colour: white, Self-adhesive | |
| GTIN (EAN) | 4032248402731 | | |
| Qty. | 200 ST | | |