

DGSB IP30 D0 PT6

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Intelligent cabling solutions can save you valuable time and money.
The FieldPower® modular system contains the right solution for every cabling task.

Foldable seals for the use of pre-assembled cables
Seals available with M16 and M20 connection thread
Integration of operating and signalling devices into the seal possible

General ordering data

Version	Field Power® sealing insert, Blank seal, IP30, with corresponding enclosure, TPE-U
Order No.	1967600000
Type	DGSB IP30 D0 PT6
GTIN (EAN)	4032248688746
Qty.	10 items

DGSB IP30 D0 PT6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	3.15 mm	Depth (inches)	0.124 inch
Height	23.51 mm	Height (inches)	0.9256 inch
Width	35 mm	Width (inches)	1.378 inch
Net weight	1.6 g		

Temperatures

Storage temperature -40 °C...55 °C Operating temperature -40 °C...55 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Basic material	TPE-U	Silicone	No
Colour	grey	Design	Blank seal
Protection degree	IP30, with corresponding enclosure	Mounting position, installation notice	in FieldPower® IP30 sealing slot

Classifications

ETIM 8.0	EC002624	ETIM 9.0	EC002624
ETIM 10.0	EC002624	ECLASS 14.0	27-18-28-15
ECLASS 15.0	27-18-28-15		