

**IE-BHD-VAPM**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



PushPull Power plug-in connector according to PROFINET specification

**General ordering data**

Version	Power connector, Device flange, PROFINET
Order No.	<a href="#">2493490000</a>
Type	IE-BHD-VAPM
GTIN (EAN)	4050118529104
Qty.	1 items

## Technical data

### Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (UR) E92202

### Dimensions and weights

Height	42 mm	Height (inches)	1.6535 inch
Width	36.2 mm	Width (inches)	1.4252 inch
Length	14.2 mm	Length (inches)	0.5591 inch
Net weight	23 g		

### Temperatures

Storage temperature	Operating temperature	-40 °C...80 °C
Installation temperature		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Shielding	unshielded	Colour	Silver grey
Housing main material	Zinc diecast, nickel-plated	Type of mounting	4 screws
Protection degree	IP67	Plugging cycles	500
Pollution severity	2	Sealing material	NBR
Type of interlock	Push Pull		

### General standards


Certificate No. (UR)	E92202
----------------------	--------

### Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

Drawings

Dimensioned drawing



Installation cut-out

