


CABTITE FRL 4-1 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The frame, fabricated from a single piece, is quick and easy to assemble and consists of dimensionally stable, fibre-glass reinforced plastic. The captive foamed seal guarantees effective IP66 sealing in accordance with DIN EN 60529, even on painted and rough surfaces.

General ordering data

| | |
|------------|---|
| Version | Locking frame, Cabtite (cable entry system), Polyamide, glass fibre-reinforced, Deep black, Height: 68.8 mm, Width: 80 mm, Depth: 11.3 mm, -40 °C... 120 °C, IP66 |
| Order No. | 2584260000 |
| Type | CABTITE FRL 4-1 BK |
| GTIN (EAN) | 4050118616200 |
| Qty. | 10 items |

CABTITE FRL 4-1 BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E223801

Dimensions and weights

| | | | |
|-----------------------------|-------------|----------------------------|-------------|
| Depth | 11.3 mm | Depth (inches) | 0.4449 inch |
| Height | 68.8 mm | Height (inches) | 2.7087 inch |
| Height of lowest version | 11.3 mm | Width | 80 mm |
| Width (inches) | 3.1496 inch | Diameter | 5.5 mm |
| Mounting dimension - height | 58 mm | Mounting dimension - width | 32 mm |
| Net weight | 22.88 g | | |

Temperatures

Operating temperature -40 °C... 120 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

General information

| | | | |
|---------------------------|---------|----------------|-----------------------------------|
| Tightening torque | 3 Nm | Silicone | No |
| UL 94 flammability rating | V-0 | Halogen | No |
| Protection degree | IP66 | Basic material | Polyamide, glass fibre-reinforced |
| Opening length | 39.8 mm | Opening width | 40 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002624 | ETIM 9.0 | EC002624 |
| ETIM 10.0 | EC002624 | ECLASS 14.0 | 27-18-28-15 |
| ECLASS 15.0 | 27-18-28-15 | | |

CABTITE FRL 4-1 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Dimensioned drawing

