


HDC MHP200 PE FC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

General ordering data

Version	Power module, 1000 V, 200 A, Number of poles: 1, Crimp connection, Female, Required plug-in slots: 1
Order No.	2637310000
Type	HDC MHP200 PE FC
GTIN (EAN)	4064675269151
Qty.	1 items

HDC MHP200 PE FC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

Depth	34 mm	Depth (inches)	1.3386 inch
Height	38.2 mm	Height (inches)	1.5039 inch
Width	21.85 mm	Width (inches)	0.8602 inch
Net weight	66.5 g		

Temperatures

Limit temperature -40 °C ... 125 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Number of poles	1	UL 94 flammability rating	V-0
Plugging cycles	≥ 500	Type	Female
Basic material	Zinc	Rated voltage (DIN EN 61984)	1000 V
Rated current (DIN EN 61984)	200 A	Required plug-in slots	1

Version

Type of connection Crimp connection
 Conductor cross-section, min. 25 mm²
 Conductor cross-section, max. 70 mm²

Signal contact

Rated voltage (DIN EN 61984), signal contact 1000 V
 Rated current (DIN EN 61984), signal contact 200 A

Classifications


ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-17
ECLASS 15.0	27-44-02-17		

HDC MHP200 PE FC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



HDC MHP200 PE FC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

200 A crimp contacts



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Type	HDC MHP200 F 25	Version
Order No.	2514820000	Female, silver, 25 - 25 mm ²
GTIN (EAN)	4050118528466	
Qty.	10 ST	
Type	HDC MHP200 F 35	Version
Order No.	2514830000	Female, silver, 35 - 35 mm ²
GTIN (EAN)	4050118528473	
Qty.	10 ST	
Type	HDC MHP200 F 50	Version
Order No.	2514840000	Female, silver, 50 - 50 mm ²
GTIN (EAN)	4050118528480	
Qty.	10 ST	
Type	HDC MHP200 F 70	Version
Order No.	2514850000	Female, silver, 70 - 70 mm ²
GTIN (EAN)	4050118528497	
Qty.	10 ST	

Miscellaneous



In addition to heavy-duty connectors, RockStar® includes the appropriate accessories for effective, functional and safe system cabling; e.g. coding systems, shield clamps, cover plates and replacement seals

General ordering data

Type	HDC MHP200 REMOVAL TOOL	Version
Order No.	2617240000	
GTIN (EAN)	4050118705430	
Qty.	1 ST	