

CABTITE BP 6MM PA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The blanking plugs are used for the safe closing of unneeded cable passages in the sealing elements.

General ordering data

| | |
|------------|---|
| Version | Blind plug, Cabtite (cable entry system), Polyamide, white, Height: 16 mm, Width: 6 mm, Depth: 16 mm, -40 °C...120 °C, IP66 |
| Order No. | 2652340000 |
| Type | CABTITE BP 6MM PA |
| GTIN (EAN) | 4050118661842 |
| Qty. | 25 items |

CABTITE BP 6MM PA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|----------|-------|-----------------|-------------|
| Depth | 16 mm | Depth (inches) | 0.6299 inch |
| Height | 16 mm | Height (inches) | 0.6299 inch |
| Width | 6 mm | Width (inches) | 0.2362 inch |
| Length | 16 mm | Length (inches) | 0.6299 inch |
| Diameter | 6 mm | Net weight | 0.12 g |

Temperatures

| | |
|-----------------------|-----------------|
| Operating temperature | -40 °C...120 °C |
|-----------------------|-----------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General information

| | | | |
|----------------------------|------|----------------------------|-----------|
| Outer cable diameter, max. | 6 mm | Outer cable diameter, min. | 6 mm |
| UL 94 flammability rating | V-0 | Halogen | No |
| Protection degree | IP66 | Basic material | Polyamide |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000879 | ETIM 9.0 | EC000879 |
| ETIM 10.0 | EC000879 | ECLASS 14.0 | 27-14-08-07 |
| ECLASS 15.0 | 27-14-08-07 | | |