


**SCCB TTB 6/4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The comprehensive accessories of the Klippon® Connect TTB-Range are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms. All function- and safety-relevant components are captively connected to the terminal block. This increases the reliability of the current and voltage transformer circuits during installation and maintenance work.

**General ordering data**

Version	Cross-connector (terminal), Plugged, orange, 30 A, Number of poles: 4, Pitch in mm (P): 8.10, Insulated: Yes, Width: 32.2 mm
Order No.	<a href="#">2710210000</a>
Type	SCCB TTB 6/4
GTIN (EAN)	4050118848007
Qty.	25 items

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	13.47 mm	Depth (inches)	0.5303 inch
Height	14.06 mm	Height (inches)	0.5535 inch
Width	32.2 mm	Width (inches)	1.2677 inch
Net weight	5.6 g		

### Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	Wemid	Colour	orange
----------------	-------	--------	--------

### System specifications

Version	Cross-connector
---------	-----------------

### Additional technical data

Type of fixing	Plugged	Explosion-tested version	No
Type of mounting	Plugged		

### Dimensions

Pitch in mm (P)	8.10 mm
-----------------	---------

### General

Number of poles	4
-----------------	---

### Rating data

Rated voltage	500 V	Nominal current	30 A
---------------	-------	-----------------	------

### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		