


SET BSCZ/SSC 4.00/10/90/3.2 SN BK SO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

| | |
|------------|--|
| Order No. | 2761040000 |
| Type | SET BSCZ/SSC 4.00/10/90/3.2 SN BK SO |
| GTIN (EAN) | 4064675048350 |
| Qty. | 50 items |
| Packaging | Box |

SET BSCZ/SSC 4.00/10/90/3.2 SN BK SO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E60693

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 15.7 mm | Depth (inches) | 0.6181 inch |
| Height | 25.2 mm | Height (inches) | 0.9921 inch |
| Width | 41.03 mm | Width (inches) | 1.6154 inch |
| Net weight | 19.1 g | | |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 18d33292-e933-40ac-8dbe-4904ce2c4ae7 |

Material data

| | | | |
|-----------------------------|----------|-----------------------------|----------|
| Insulating material | PA | Colour | black |
| Colour chart (similar) | RAL 9011 | Moisture Level (MSL) | |
| UL 94 flammability rating | V-0 | Contact material | Cu-alloy |
| Contact surface | tinned | Operating temperature, min. | -50 °C |
| Operating temperature, max. | 120 °C | | |

Rated data acc. to IEC

| | | | |
|--|--------|---|--------|
| Rated current, max. number of poles (Tu=20°C) | 13.5 A | Rated current, min. number of poles (Tu=40°C) | 16.5 A |
| Rated voltage for surge voltage class / pollution degree II/2 | 600 V | Rated voltage for surge voltage class / pollution degree III/2 | 300 V |
| Rated impulse voltage for surge voltage class/ pollution degree II/2 | 4000 V | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 4000 V |

Rated data acc. to UL 1059

| | | | |
|------------------------------|--|-------------------------|--------|
| Institute (cURus) | CURUS | Certificate No. (cURus) | E60693 |
| Reference to approval values | Specifications are maximum values, details - see approval certificate. | | |

Packing

| | | | |
|-----------|-----------|------------|-----------|
| Packaging | Box | VPE length | 502.00 mm |
| VPE width | 389.00 mm | VPE height | 220.00 mm |

Important note

Notes

SET BSCZ/SSC 4.00/10/90/3.2 SN BK SO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002643 | ETIM 9.0 | EC002643 |
| ETIM 10.0 | EC002643 | ECLASS 14.0 | 27-46-01-01 |
| ECLASS 15.0 | 27-46-01-01 | | |