

IE-ANT-CELL-SISO-EO-SMAM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Antennas and antenna accessories (coax cables and mounts)

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

General ordering data

Version	Omni-directional antenna, Cellular antenna, Up to 5G (support for frequencies below 2.7 GHz, e.g., bands n1, n2, n28), Vertical, SMA male, IP66, Impedance: 50 Ω
Order No.	2788130000
Type	IE-ANT-CELL-SISO-EO-SMAM
GTIN (EAN)	4064675066392
Qty.	1 items

IE-ANT-CELL-SISO-EO-SMAM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	208 mm	Height (inches)	8.189 inch
Net weight	46.58 g		

Temperatures

Storage temperature	-40 °C...75 °C	Operating temperature	-40 °C...75 °C
---------------------	----------------	-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	e4cad7fc-a55e-4d5c-8f05-417a6385e9b6

Enclosure material

Colour	black
--------	-------

Included in delivery

Included in delivery	1 x antenna
----------------------	-------------

Technical data

Type of connection	SMA male	Impedance	50 Ω
Standing wave ratio	1.5 typical / 2.0 max	Composite power max.	10 W
Frequency range	690-950 MHz, 1.7-3.8 GHz	Antenna gain	2 dBi
Polarisation	Vertical		

Environmental conditions

Operating temperature, max.	75 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	75 °C	Storage temperature, min.	-40 °C

Classifications

ETIM 8.0	EC001698	ETIM 9.0	EC001698
ETIM 10.0	EC001698	ECLASS 14.0	19-07-01-07
ECLASS 15.0	19-07-01-07		

IE-ANT-CELL-SISO-EO-SMAM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Antennas and antenna accessories (coax cables and mounts)



Antennas and antenna accessories (coax cables and mounts)

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

General ordering data

Type	IE-CC-SMAM-SMAF-1M	Version
Order No.	2787920000	Antenna cable, Connection 1:, SMA male, Connection 2:, SMA
GTIN (EAN)	4064675066088	female, Length: 1 m
Qty.	1 ST	
Type	IE-CC-SMAM-SMAF-3M	Version
Order No.	2787930000	Antenna cable, Connection 1:, SMA male, Connection 2:, SMA
GTIN (EAN)	4064675066095	female, Length: 3 m
Qty.	1 ST	
Type	IE-CC-SMAM-SMAF-5M	Version
Order No.	2787940000	Antenna cable, Connection 1:, SMA male, Connection 2:, SMA
GTIN (EAN)	4064675066200	female, Length: 5 m
Qty.	1 ST	