


**WIL-F-240**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



UV filter for additional screwing to the Weidmüller Industry Light.

**General ordering data**

Order No.	2799050000
Type	<a href="#">WIL-F-240</a>
GTIN (EAN)	4064675259084
Qty.	4 items

**WIL-F-240**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	38.5 mm	Depth (inches)	1.5157 inch
Height	2.2 mm	Height (inches)	0.0866 inch
Width	240 mm	Width (inches)	9.4488 inch
Net weight	34.5 g		

**Temperatures**

Operating temperature	-
-----------------------	---



**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Classifications**

ETIM 8.0	EC002558	ETIM 9.0	EC002558
ETIM 10.0	EC002558	ECLASS 14.0	27-11-11-25
ECLASS 15.0	27-11-11-25		

Drawings



**WIL-F-240**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Counterpart**

**Housing length 240 mm**



**240 mm**

The WIL-LED lights family: Only 8mm (9.4mm with magnet) high LED lamp for 24V DC with very high luminous efficacy and high lifespan (greater 60 000h). Very robust construction, by full potting and metal housing - waterproof (IP67). Due to its 6500K light color (daylight) suitable for the various applications. Optionally easily connectable with M12 connection. Due to the low power consumption, a small enough power supply with 24V for operation.

**General ordering data**

Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2436210000</a>
GTIN (EAN)	4050118448306
Qty.	1 ST
Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2527880000</a>
GTIN (EAN)	4050118538762
Qty.	1 ST
Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2527890000</a>
GTIN (EAN)	4050118538670
Qty.	1 ST
Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2527900000</a>
GTIN (EAN)	4050118538687
Qty.	1 ST
Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2527910000</a>
GTIN (EAN)	4050118538694
Qty.	1 ST
Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2527950000</a>
GTIN (EAN)	4050118538939
Qty.	1 ST
Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2527990000</a>
GTIN (EAN)	4050118538977
Qty.	1 ST
Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2527920000</a>
GTIN (EAN)	4050118538908
Qty.	1 ST
Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2527960000</a>
GTIN (EAN)	4050118538946
Qty.	1 ST
Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2527930000</a>
GTIN (EAN)	4050118538915
Qty.	1 ST

## WIL-F-240

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Counterpart

Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2527940000</a>
GTIN (EAN)	4050118538922
Qty.	1 ST
Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2527970000</a>
GTIN (EAN)	4050118538953
Qty.	1 ST
Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2527980000</a>
GTIN (EAN)	4050118538960
Qty.	1 ST
Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2669240000</a>
GTIN (EAN)	4050118682601
Qty.	1 ST

## Housing length 145 mm



145 mm

The WIL-LED lights family: Only 8mm (9.4mm with magnet) high LED lamp for 24V DC with very high luminous efficacy and high lifespan (greater 60 000h). Very robust construction, by full potting and metal housing - waterproof (IP67). Due to its 6500K light color (daylight) suitable for the various applications. Optionally easily connectable with M12 connection. Due to the low power consumption, a small enough power supply with 24V for operation.

## General ordering data

Type	WIL-LWXXXX-6500D024-145... Version
Order No.	<a href="#">2669230000</a>
GTIN (EAN)	4050118682618
Qty.	1 ST

## Housing length 240 mm



240 mm

The WIL-LED lights family: Only 8mm (9.4mm with magnet) high LED lamp for 24V DC with very high luminous efficacy and high lifespan (greater 60 000h). Very robust construction, by full potting and metal housing - waterproof (IP67). Due to its 6500K light color (daylight) suitable for the various applications. Optionally easily connectable with M12 connection. Due to the low power consumption, a small enough power supply with 24V for operation.

## General ordering data

Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2528030000</a>
GTIN (EAN)	4050118539011
Qty.	1 ST

**WIL-F-240****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Counterpart**

Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2528020000</a>
GTIN (EAN)	4050118539004
Qty.	1 ST
Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2528010000</a>
GTIN (EAN)	4050118538991
Qty.	1 ST
Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2528000000</a>
GTIN (EAN)	4050118538984
Qty.	1 ST
Type	WIL-LWXXXX-6500D024-240... Version
Order No.	<a href="#">2576960000</a>
GTIN (EAN)	4050118592863
Qty.	1 ST
Type	WIL-LWXXXX-4000D024-240... Version
Order No.	<a href="#">2617810000</a>
GTIN (EAN)	4050118649185
Qty.	1 ST
Type	WIL-LWXXXX-4000D024-240... Version
Order No.	<a href="#">2770730000</a>
GTIN (EAN)	4064675030799
Qty.	1 ST
Type	WIL-LWXXXX-4000D024-240... Version
Order No.	<a href="#">2732910000</a>
GTIN (EAN)	4050118811797
Qty.	1 ST
Type	WIL-LWXXXX-2700D024-240... Version
Order No.	<a href="#">2633830000</a>
GTIN (EAN)	4050118648959
Qty.	1 ST
Type	WIL-LWXXXX-2700D024-240... Version
Order No.	<a href="#">2680950000</a>
GTIN (EAN)	4050118694710
Qty.	1 ST