

US67-PLATE64-STD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Weidmüller offers high-quality cables, plugs, mounting adapters and magnets for the professional and industrial installation of vibration monitors.

General ordering data

Version	Adapter plate
Order No.	2811910000
Type	US67-PLATE64-STD
GTIN (EAN)	4064675292975
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2025-07-30T00:00:00+02:00

US67-PLATE64-STD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	64 mm	Depth (inches)	2.5197 inch
Height	11.5 mm	Height (inches)	0.4528 inch
Width	64 mm	Width (inches)	2.5197 inch
Diameter	64 mm	Net weight	116.16 g

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-20 °C...85 °C
Humidity at operating temperature	5...95 % rel. humidity, no condensation		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of accessory	Mounting accessories	Is an accessory	Yes
-------------------	----------------------	-----------------	-----

Installation

Type of thread	metric
----------------	--------

Classifications

ETIM 8.0	EC003015	ETIM 9.0	EC003015
ETIM 10.0	EC003015	ECLASS 14.0	27-20-14-92
ECLASS 15.0	27-20-14-92		

US67-PLATE64-STD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

