

ESG-LP 6/17 MM SI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

| | |
|------------|--|
| Version | ESG, Device markers, 6 x 17 mm, silver |
| Order No. | 288580000 |
| Type | ESG-LP 6/17 MM SI |
| GTIN (EAN) | 4064675854401 |
| Qty. | 24000 items |

ESG-LP 6/17 MM SI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 0.05 mm | Depth (inches) | 0.002 inch |
| Height | 6 mm | Height (inches) | 0.2362 inch |
| Width | 17 mm | Width (inches) | 0.6693 inch |
| Net weight | 0.01 g | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|-----------------------------------|-------------------|-----------------------------------|-----------------------------|
| Adhesive | Acrylate adhesive | Version | Self-adhesive, halogen-free |
| Width | 17 mm | UL 94 flammability rating | V-0 |
| Operating temperature range, max. | 150 °C | Operating temperature range, min. | -40 °C |
| Colour | silver | Halogen | No |
| Basic material | Polyamide | Printed characters | without |
| Approval acc. to UL 969 | Yes | | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

Drawings

