

**RC M P3 M20 C****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The circular connectors with click system enable a quick connection with a high protection class. They are available both as plugs and sockets.

**General ordering data**

Order No.	2891850000
Type	<a href="#">RC M P3 M20 C</a>
GTIN (EAN)	4064675881278

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E307231

Dimensions and weights

Diameter	20 mm	Net weight	0.01 g
----------	-------	------------	--------

Temperatures

Storage temperature	Operating temperature	-40 °C...60 °C
---------------------	-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	b64e9137-212c-40f4-8b4a-2cb7feb25f72

Technical data customisable plug-in connectors

Number of poles	3	Coding	none
Contact surface	Brass	LED	No
Type of connection	Lever clamp, SNAP IN	Housing main material	PA 66
Cable diameter, max.	13 mm	Cable diameter, min.	7 mm
Contact material	Brass	Conductor cross-section, max.	1.5 mm <sup>2</sup>
Conductor cross-section, min.	0.25 mm <sup>2</sup>	Nominal voltage	500 V
Nominal current	17.5 A	Protection degree	IP68
Gender of contact	Male	Shield connection	No
Threaded ring material	Plastic	Connection cross-section, max.	4 mm <sup>2</sup>
Connection cross-section, min.	0.5 mm <sup>2</sup>		

General data

Number of poles	3	Connection thread	M20
Type of connection	Lever clamp, SNAP IN	Housing main material	PA 66

Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		