


APGTB 1.5 PE 4C/4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Some applications demand for a pluggable, modular solution to be more flexible or to facilitate the installation. Where complete functional units have to be prefabricated or replaced, modular and flexible connection systems are required. Our pluggable terminal blocks can be quickly assembled and are completely factory tested.

General ordering data

| | |
|------------|---|
| Version | Plug-in modular terminals, PUSH IN, 1.5 mm ² , 500 V, 17.5 A, Green/yellow |
| Order No. | 2898140000 |
| Type | APGTB 1.5 PE 4C/4 |
| GTIN (EAN) | 4064675903239 |
| Qty. | 50 items |

APGTB 1.5 PE 4C/4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E60693

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 33.5 mm | Depth (inches) | 1.3189 inch |
| Height | 80 mm | Height (inches) | 3.1496 inch |
| Width | 3.5 mm | Width (inches) | 0.1378 inch |
| Net weight | 8.45 g | | |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 130 °C |
|----------------------------------|--------|----------------------------------|--------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|---------------------------|-------|--------|--------------|
| Basic material | Wemid | Colour | Green/yellow |
| UL 94 flammability rating | V-0 | | |

System specifications

| | | | |
|-----------------------------------|-------|-------------------------------------|-----|
| End cover plate required | Yes | Number of potentials | 1 |
| Number of levels | 1 | Number of clamping points per level | 4 |
| Levels cross-connected internally | No | PE connection | Yes |
| Mounting rail | TS 35 | N-function | No |
| PE function | Yes | PEN function | No |

Additional technical data

| | | | |
|------------------|-------|--------------------------|-----|
| Open sides | right | Explosion-tested version | Yes |
| Type of mounting | TS 35 | | |

Conductors for clamping (additional connection)

Connection type, additional connection pluggable

Conductors for clamping (rated connection)

| | | | |
|---|---------------------|---|----------------------|
| Wire connection cross section AWG, max. | AWG 14 | Connection direction | top |
| Type of connection | PUSH IN | Number of connections | 4 |
| Clamping range, max. | 1.5 mm ² | Clamping range, min. | 0.14 mm ² |
| Wire connection cross section AWG, min. | AWG 26 | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 2.5 mm ² |

APGTB 1.5 PE 4C/4

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

| | | | |
|---|----------------------|---|---------------------|
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.14 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 2.5 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.14 mm ² | Wire connection cross section, finely stranded, max. | 2.5 mm ² |
| Wire connection cross section, finely stranded, min. | 0.14 mm ² | Connection cross-section, stranded, max. | 4 mm ² |
| Connection cross-section, stranded, min. | 0.14 mm ² | Wire connection cross-section, solid core, max. | 2.5 mm ² |
| Wire connection cross-section, solid core, min. | 0.14 mm ² | | |

General

| | | | |
|---|--------|---|--------|
| Wire connection cross section AWG, max. | AWG 14 | Wire connection cross section AWG, min. | AWG 26 |
| Mounting rail | TS 35 | | |

Rating data

| | | | |
|---------------------------------|---------------------|--|---------|
| Rated cross-section | 1.5 mm ² | Rated voltage | 500 V |
| Rated DC voltage | 500 V | Nominal current | 17.5 A |
| Current at maximum wires | 17.5 A | Volume resistance according to IEC 60947-7-x | 1.83 mΩ |
| Rated impulse withstand voltage | 6 kV | Power loss in accordance with IEC 60947-7-x | 0.56 mW |
| Surge voltage category | III | Pollution severity | 3 |


UL rating data

| | | | |
|--|--------|--|--------|
| Conductor size Factory wiring max. (cURus) | 14 AWG | Voltage size B (cURus) | 300 V |
| Voltage size D (cURus) | 600 V | Certificate No. (cURus) | E60693 |
| Conductor size Field wiring min. (cURus) | 26 AWG | Conductor size Factory wiring min. (cURus) | 26 AWG |
| Voltage size C (cURus) | 300 V | Conductor size Field wiring max. (cURus) | 14 AWG |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000897 | ETIM 9.0 | EC000897 |
| ETIM 10.0 | EC000897 | ECLASS 14.0 | 27-25-01-17 |
| ECLASS 15.0 | 27-25-01-17 | | |

Drawings



APGTB 1.5 PE 4C/4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Plugs




The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | APGPC 1.5 | Version |
| Order No. | 2482530000 | Terminal cover, orange, Wemid, Height: 16 mm, Width: 3.3 mm, |
| GTIN (EAN) | 4050118494563 | Depth: 13 mm, V-0 |
| Qty. | 50 ST | |
| Type | APGCE | Version |
| Order No. | 1514490000 | Coding element (terminal), Wemid, orange, Width: 3.3 mm |
| GTIN (EAN) | 4050118321906 | |
| Qty. | 50 ST | |

Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | ZQV 1.5N/10 | Version |
| Order No. | 1985580000 | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of poles: 10, Pitch in mm (P): 3.50, Insulated: Yes, Width: 33.5 mm |
| GTIN (EAN) | 4050118370416 | |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/10 BL | Version |
| Order No. | 1985680000 | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 10, Pitch in mm (P): 3.50, Insulated: Yes, Width: 33.5 mm |
| GTIN (EAN) | 4050118370539 | |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/10 RD | Version |
| Order No. | 1985800000 | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 10, Pitch in mm (P): 3.50, Insulated: Yes, Width: 33.5 mm |
| GTIN (EAN) | 4050118370393 | |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/2 | Version |
| Order No. | 1985410000 | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of poles: 2, Pitch in mm (P): 3.50, Insulated: Yes, Width: 5.5 mm |
| GTIN (EAN) | 4050118369861 | |
| Qty. | 60 ST | |

APGTB 1.5 PE 4C/4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--|
| Type | ZQV 1.5N/2 BL | Version |
| Order No. | 1985530000 | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 2, |
| GTIN (EAN) | 4050118370423 | Pitch in mm (P): 3.50, Insulated: Yes, Width: 5.5 mm |
| Qty. | 60 ST | |
| Type | ZQV 1.5N/2 RD | Version |
| Order No. | 1985650000 | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 2, |
| GTIN (EAN) | 4050118370324 | Pitch in mm (P): 3.50, Insulated: Yes, Width: 5.5 mm |
| Qty. | 60 ST | |
| Type | ZQV 1.5N/20 | Version |
| Order No. | 1985600000 | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of |
| GTIN (EAN) | 4050118370225 | poles: 20, Pitch in mm (P): 3.50, Insulated: Yes, Width: 70 mm |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/20 BL | Version |
| Order No. | 1985700000 | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: |
| GTIN (EAN) | 4050118370331 | 20, Pitch in mm (P): 3.50, Insulated: Yes, Width: 70 mm |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/20 RD | Version |
| Order No. | 1985810000 | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: |
| GTIN (EAN) | 4050118370355 | 20, Pitch in mm (P): 3.50, Insulated: Yes, Width: 70 mm |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/3 | Version |
| Order No. | 1985480000 | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of |
| GTIN (EAN) | 4050118370096 | poles: 3, Pitch in mm (P): 3.50, Insulated: Yes, Width: 9 mm |
| Qty. | 60 ST | |
| Type | ZQV 1.5N/3 BL | Version |
| Order No. | 1985550000 | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 3, |
| GTIN (EAN) | 4050118370485 | Pitch in mm (P): 3.50, Insulated: Yes, Width: 9 mm |
| Qty. | 60 ST | |
| Type | ZQV 1.5N/3 RD | Version |
| Order No. | 1985670000 | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 3, |
| GTIN (EAN) | 4050118370348 | Pitch in mm (P): 3.50, Insulated: Yes, Width: 9 mm |
| Qty. | 60 ST | |
| Type | ZQV 1.5N/4 | Version |
| Order No. | 1985490000 | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of |
| GTIN (EAN) | 4050118370201 | poles: 4, Pitch in mm (P): 3.50, Insulated: Yes, Width: 12.5 mm |
| Qty. | 60 ST | |
| Type | ZQV 1.5N/4 BL | Version |
| Order No. | 1985570000 | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 4, |
| GTIN (EAN) | 4050118370317 | Pitch in mm (P): 3.50, Insulated: Yes, Width: 12.5 mm |
| Qty. | 60 ST | |
| Type | ZQV 1.5N/4 RD | Version |
| Order No. | 1985690000 | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 4, |
| GTIN (EAN) | 4050118370515 | Pitch in mm (P): 3.50, Insulated: Yes, Width: 12.5 mm |
| Qty. | 60 ST | |
| Type | ZQV 1.5N/5 | Version |
| Order No. | 1985500000 | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of |
| GTIN (EAN) | 4050118369991 | poles: 5, Pitch in mm (P): 3.50, Insulated: Yes, Width: 16 mm |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/5 BL | Version |
| Order No. | 1985590000 | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 5, |
| GTIN (EAN) | 4050118370430 | Pitch in mm (P): 3.50, Insulated: Yes, Width: 16 mm |
| Qty. | 20 ST | |

APGTB 1.5 PE 4C/4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--|
| Type | ZQV 1.5N/5 RD | Version |
| Order No. | 1985710000 | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 5, |
| GTIN (EAN) | 4050118370256 | Pitch in mm (P): 3.50, Insulated: Yes, Width: 16 mm |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/50 | Version |
| Order No. | 1985620000 | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of |
| GTIN (EAN) | 4050118370300 | poles: 50, Pitch in mm (P): 3.50, Insulated: Yes, Width: 175 mm |
| Qty. | 5 ST | |
| Type | ZQV 1.5N/50 BL | Version |
| Order No. | 1985720000 | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: |
| GTIN (EAN) | 4050118370546 | 50, Pitch in mm (P): 3.50, Insulated: Yes, Width: 175 mm |
| Qty. | 5 ST | |
| Type | ZQV 1.5N/50 RD | Version |
| Order No. | 1985820000 | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: |
| GTIN (EAN) | 4050118370270 | 50, Pitch in mm (P): 3.50, Insulated: Yes, Width: 175 mm |
| Qty. | 5 ST | |
| Type | ZQV 1.5N/6 | Version |
| Order No. | 1985510000 | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of |
| GTIN (EAN) | 4050118370188 | poles: 6, Pitch in mm (P): 3.50, Insulated: Yes, Width: 19.5 mm |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/6 BL | Version |
| Order No. | 1985610000 | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 6, |
| GTIN (EAN) | 4050118370492 | Pitch in mm (P): 3.50, Insulated: Yes, Width: 19.5 mm |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/6 RD | Version |
| Order No. | 1985730000 | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 6, |
| GTIN (EAN) | 4050118370454 | Pitch in mm (P): 3.50, Insulated: Yes, Width: 19.5 mm |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/7 | Version |
| Order No. | 1985520000 | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of |
| GTIN (EAN) | 4050118370195 | poles: 7, Pitch in mm (P): 3.50, Insulated: Yes, Width: 23 mm |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/7 BL | Version |
| Order No. | 1985630000 | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 7, |
| GTIN (EAN) | 4050118370522 | Pitch in mm (P): 3.50, Insulated: Yes, Width: 23 mm |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/7 RD | Version |
| Order No. | 1985750000 | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 7, |
| GTIN (EAN) | 4050118370249 | Pitch in mm (P): 3.50, Insulated: Yes, Width: 23 mm |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/8 | Version |
| Order No. | 1985540000 | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of |
| GTIN (EAN) | 4050118370218 | poles: 8, Pitch in mm (P): 3.50, Insulated: Yes, Width: 26.5 mm |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/8 BL | Version |
| Order No. | 1985640000 | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 8, |
| GTIN (EAN) | 4050118370461 | Pitch in mm (P): 3.50, Insulated: Yes, Width: 26.5 mm |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/8 RD | Version |
| Order No. | 1985770000 | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 8, |
| GTIN (EAN) | 4050118370508 | Pitch in mm (P): 3.50, Insulated: Yes, Width: 26.5 mm |
| Qty. | 20 ST | |

APGTB 1.5 PE 4C/4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--|
| Type | ZQV 1.5N/9 | Version |
| Order No. | 1985560000 | Cross-connector (terminal), Plugged, orange, 17.5 A, Number of poles: 9, Pitch in mm (P): 3.50, Insulated: Yes, Width: 30 mm |
| GTIN (EAN) | 4050118370409 | |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/9 BL | Version |
| Order No. | 1985660000 | Cross-connector (terminal), Plugged, blue, 17.5 A, Number of poles: 9, Pitch in mm (P): 3.50, Insulated: Yes, Width: 30 mm |
| GTIN (EAN) | 4050118370478 | |
| Qty. | 20 ST | |
| Type | ZQV 1.5N/9 RD | Version |
| Order No. | 1985790000 | Cross-connector (terminal), Plugged, red, 17.5 A, Number of poles: 9, Pitch in mm (P): 3.50, Insulated: Yes, Width: 30 mm |
| GTIN (EAN) | 4050118370386 | |
| Qty. | 20 ST | |

End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

| | | |
|------------|----------------------------|-----------------------|
| Type | AEB 35 SCL/1 V0 | Version |
| Order No. | 2661280000 | A-series, End bracket |
| GTIN (EAN) | 4050118702163 | |
| Qty. | 20 ST | |
| Type | AEB 35 SCL/1 V0 BK | Version |
| Order No. | 2661300000 | A-series, End bracket |
| GTIN (EAN) | 4050118702187 | |
| Qty. | 20 ST | |
| Type | AEB 35 SCL/1 V0 BK DL | Version |
| Order No. | 2570250000 | A-series, End bracket |
| GTIN (EAN) | 4050118580266 | |
| Qty. | 50 ST | |

End plates and partition plates



Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

APGTB 1.5 PE 4C/4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

| | | | |
|------------|----------------------------|---------------------|--|
| Type | AEP PGTB 1.5 4C/4 | Version | |
| Order No. | 2898180000 | A-series, End plate | |
| GTIN (EAN) | 4064675903277 | | |
| Qty. | 20 ST | | |

Plugs



The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | APGLE 1.5 | Version | |
| Order No. | 2482720000 | Locking clips (terminal), Wemid, orange | |
| GTIN (EAN) | 4050118496253 | | |
| Qty. | 25 ST | | |
| Type | APG 1.5 L | Version | |
| Order No. | 2482250000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 1, dark beige | |
| GTIN (EAN) | 4050118494280 | | |
| Qty. | 50 ST | | |
| Type | APG 1.5 L BL | Version | |
| Order No. | 2482260000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 1, blue | |
| GTIN (EAN) | 4050118494297 | | |
| Qty. | 50 ST | | |
| Type | APG 1.5 L GN | Version | |
| Order No. | 2482270000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 1, green | |
| GTIN (EAN) | 4050118494303 | | |
| Qty. | 50 ST | | |
| Type | APG 1.5 MI | Version | |
| Order No. | 2482280000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 1, dark beige | |
| GTIN (EAN) | 4050118494310 | | |
| Qty. | 50 ST | | |
| Type | APG 1.5 MI BL | Version | |
| Order No. | 2482290000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 1, blue | |
| GTIN (EAN) | 4050118494327 | | |
| Qty. | 50 ST | | |
| Type | APG 1.5 MI GN | Version | |
| Order No. | 2482300000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 1, green | |
| GTIN (EAN) | 4050118494365 | | |
| Qty. | 50 ST | | |
| Type | APG 1.5 R | Version | |
| Order No. | 2482310000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 1, dark beige | |
| GTIN (EAN) | 4050118494372 | | |
| Qty. | 50 ST | | |

APGTB 1.5 PE 4C/4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--|
| Type | APG 1.5 R BL | Version |
| Order No. | 2482320000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 1, blue |
| GTIN (EAN) | 4050118494389 | |
| Qty. | 50 ST | |
| Type | APG 1.5 R GN | Version |
| Order No. | 2482330000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 1, green |
| GTIN (EAN) | 4050118494396 | |
| Qty. | 50 ST | |
| Type | APG 1.5/1 | Version |
| Order No. | 2482340000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 1, dark beige |
| GTIN (EAN) | 4050118494402 | |
| Qty. | 50 ST | |
| Type | APG 1.5/10 | Version |
| Order No. | 2482430000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 10, dark beige |
| GTIN (EAN) | 4050118494495 | |
| Qty. | 20 ST | |
| Type | APG 1.5/10-9BG-GN | Version |
| Order No. | 2719830000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 10, dark beige |
| GTIN (EAN) | 4050118811292 | |
| Qty. | 20 ST | |
| Type | APG 1.5/2 | Version |
| Order No. | 2482350000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 2, dark beige |
| GTIN (EAN) | 4050118494419 | |
| Qty. | 25 ST | |
| Type | APG 1.5/3 | Version |
| Order No. | 2482360000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 3, dark beige |
| GTIN (EAN) | 4050118494426 | |
| Qty. | 25 ST | |
| Type | APG 1.5/3-2BG-GN | Version |
| Order No. | 2719740000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 3, dark beige |
| GTIN (EAN) | 4050118811438 | |
| Qty. | 25 ST | |
| Type | APG 1.5/3-BG-BL-GN | Version |
| Order No. | 2482460000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 3, dark beige |
| GTIN (EAN) | 4050118494525 | |
| Qty. | 25 ST | |
| Type | APG 1.5/4 | Version |
| Order No. | 2482370000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 4, dark beige |
| GTIN (EAN) | 4050118494433 | |
| Qty. | 25 ST | |
| Type | APG 1.5/4-3BG-GN | Version |
| Order No. | 2482450000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 4, dark beige |
| GTIN (EAN) | 4050118494518 | |
| Qty. | 25 ST | |
| Type | APG 1.5/4-3BG-GN | Version |
| Order No. | 2719750000 | Plug, 1.5 mm ² , 500 V, 17.5 A, dark beige, green |
| GTIN (EAN) | | |
| Qty. | 25 ST | |
| Type | APG 1.5/5 | Version |
| Order No. | 2482380000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 5, dark beige |
| GTIN (EAN) | 4050118494440 | |
| Qty. | 25 ST | |

APGTB 1.5 PE 4C/4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|---|
| Type | APG 1.5/5-3BG-BL-GN | Version |
| Order No. | 2482440000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 5, dark beige |
| GTIN (EAN) | 4050118494501 | |
| Qty. | 25 ST | |
| Type | APG 1.5/5-4BG-GN | Version |
| Order No. | 2719770000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 5, dark beige |
| GTIN (EAN) | 4050118811421 | |
| Qty. | 25 ST | |
| Type | APG 1.5/6 | Version |
| Order No. | 2482390000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 6, dark beige |
| GTIN (EAN) | 4050118494457 | |
| Qty. | 25 ST | |
| Type | APG 1.5/6-5BG-GN | Version |
| Order No. | 2719780000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 6, dark beige |
| GTIN (EAN) | 4050118811414 | |
| Qty. | 25 ST | |
| Type | APG 1.5/7 | Version |
| Order No. | 2482400000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 7, dark beige |
| GTIN (EAN) | 4050118494464 | |
| Qty. | 25 ST | |
| Type | APG 1.5/7-6BG-GN | Version |
| Order No. | 2719800000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 7, dark beige |
| GTIN (EAN) | 4050118811285 | |
| Qty. | 25 ST | |
| Type | APG 1.5/8 | Version |
| Order No. | 2482410000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 8, dark beige |
| GTIN (EAN) | 4050118494471 | |
| Qty. | 20 ST | |
| Type | APG 1.5/8-7BG-GN | Version |
| Order No. | 2719810000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 8, dark beige |
| GTIN (EAN) | 4050118811179 | |
| Qty. | 20 ST | |
| Type | APG 1.5/9 | Version |
| Order No. | 2482420000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 9, dark beige |
| GTIN (EAN) | 4050118494488 | |
| Qty. | 20 ST | |
| Type | APG 1.5/9-8BG-GN | Version |
| Order No. | 2719820000 | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 9, dark beige |
| GTIN (EAN) | 4050118811407 | |
| Qty. | 20 ST | |
| Type | APGSR 1.5 | Version |
| Order No. | 2482730000 | Strain relief (terminal), Wemid, orange |
| GTIN (EAN) | 4050118493993 | |
| Qty. | 25 ST | |
| Type | APGSR 1.5 - 4P | Version |
| Order No. | 2482740000 | Strain relief (terminal), Wemid, orange |
| GTIN (EAN) | 4050118494204 | |
| Qty. | 25 ST | |
| Type | APGSR 1.5 - 8P | Version |
| Order No. | 2482750000 | Strain relief (terminal), Wemid, orange |
| GTIN (EAN) | 4050118494211 | |
| Qty. | 25 ST | |


APGTB 1.5 PE 4C/4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
 - Strips for fast installation
 - Terminal markers, suitable for all Weidmüller cable connectors
 - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | DEK 5/3.5 MC NE GE | Version |
| Order No. | 1369480000 | Dekafix, Terminal marker, 5 x 3.5 mm, Pitch in mm (P): 3.50 |
| GTIN (EAN) | 4050118171860 | Weidmueller, yellow |
| Qty. | 500 ST | |
| Type | DEK 5/3.5 MC NE WS | Version |
| Order No. | 1755270000 | Dekafix, Terminal marker, 5 x 3.5 mm, Pitch in mm (P): 3.50 |
| GTIN (EAN) | 4032248017348 | Weidmueller, white |
| Qty. | 500 ST | |

Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
 - Strips for fast installation
 - Terminal markers, suitable for all Weidmüller cable connectors
 - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | DEK 5/3.5 MC SDR | Version |
| Order No. | 1767730000 | Dekafix, Terminal marker, 5 x 3.5 mm, Pitch in mm (P): 3.50 |
| GTIN (EAN) | 4032248102532 | Weidmueller, To customer specification |
| Qty. | 100 ST | |


APGTB 1.5 PE 4C/4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
 - Strips for fast installation
 - Terminal markers, suitable for all Weidmüller cable connectors
 - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | DEK 5/3.5 PLUS MC NE WS | Version |
| Order No. | 2003750000 | Dekafix, Terminal marker, 5 x 3.5 mm, Pitch in mm (P): 3.50 |
| GTIN (EAN) | 4050118424430 | Weidmueller, white |
| Qty. | 1600 ST | |

Custom printing



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
 - Strips for fast installation
 - Terminal markers, suitable for all Weidmüller cable connectors
 - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | DEK 5/3.5 PLUS MC SDR | Version |
| Order No. | 2007790000 | Dekafix, Terminal marker, 5 x 3.5 mm, Pitch in mm (P): 3.50 |
| GTIN (EAN) | 4050118393347 | Weidmueller, To customer specification |
| Qty. | 320 ST | |

APGTB 1.5 PE 4C/4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Testadapter and testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | FZS 2/4 RT/80 SAKT4 | Version | |
| Order No. | 1276300000 | Plug (terminal), Plug-in connection, 2 mm ² , Number of connections: 2, | |
| GTIN (EAN) | 4008190026080 | Number of poles: 1, Width: 9 mm | |
| Qty. | 20 ST | | |