


**V-ZPA FUSE HOLDER**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



**General ordering data**

|                     |                                     |
|---------------------|-------------------------------------|
| Order No.           | 2904480000                          |
| Type                | <a href="#">V-ZPA FUSE HOLDER</a>   |
| GTIN (EAN)          | 4099986010383                       |
| Qty.                | 1 items                             |
| Delivery status     | Discontinued                        |
| Available until     | 2024-07-23T00:00:00+02:00           |
| Alternative product | <a href="#">V-ZPA FUSE HOLDER E</a> |

## V-ZPA FUSE HOLDER

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 65.5 mm | Depth (inches)  | 2.5787 inch |
| Height     | 95.2 mm | Height (inches) | 3.748 inch  |
| Width      | 18.5 mm | Width (inches)  | 0.7283 inch |
| Net weight | 144 g   |                 |             |

## Temperatures

|                     |                       |                       |                |
|---------------------|-----------------------|-----------------------|----------------|
| Storage temperature |                       | Operating temperature | -25 °C...55 °C |
| Humidity            | 5 - 95% rel. humidity |                       |                |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## General data

|                          |          |                   |              |
|--------------------------|----------|-------------------|--------------|
| Optical function display | No       | Design            | Adapter plug |
| Colour                   | grey     | Protection degree | IP00         |
| Mounting rail            | Busbar   | Acoustic signal   | No           |
| Operating altitude       | ≤ 4000 m |                   |              |

## Insulation coordination acc. to EN 50178

Pollution severity 2

## Rated data IEC / EN

|                         |       |                                    |           |
|-------------------------|-------|------------------------------------|-----------|
| Signalling contact      | No    | Rated voltage (AC)                 | 240 V     |
| Rated current IN        | 6.3 A | Voltage type                       | AC        |
| Fuse protection         | 6.3 A | Standards                          | IEC 61984 |
| Acoustic signal         | No    | Short-circuit current rating ISCCR | 25 kA     |
| Integrated back-up fuse | Yes   |                                    |           |

## Connection data

|  |                     |  |                      |
|--|---------------------|--|----------------------|
| Stripping length   | 13 mm               | Wire connection method                   | PUSH IN              |
| Clamping range, rated connection                           | 2.5 mm <sup>2</sup> | Wire cross-section, solid, max.          | 2.5 mm <sup>2</sup>  |
| Conductor cross-section, flexible, AEH (DIN 46228-1), max. | 2.5 mm <sup>2</sup> | Connection cross-section, stranded, min. | 0.82 mm <sup>2</sup> |
| Connection cross-section, stranded, max.                   | 2.5 mm <sup>2</sup> |  |                      |

## Electrical data

Voltage type AC

## General data

|                   |      |        |      |
|-------------------|------|--------|------|
| Protection degree | IP00 | Colour | grey |
|-------------------|------|--------|------|

**V-ZPA FUSE HOLDER**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000941    | ETIM 9.0    | EC000941    |
| ETIM 10.0   | EC000941    | ECLASS 14.0 | 27-17-90-90 |
| ECLASS 15.0 | 27-17-90-90 |             |             |