


THM WO-R VIN 25.4/19.1 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**General ordering data**

Version	Conductor and cable markers, 25.4 x 19.1 mm, white
Order No.	2932080000
Type	THM WO-R VIN 25.4/19.1 WS
GTIN (EAN)	4099986670808
Qty.	7450 items

THM WO-R VIN 25.4/19.1 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.07 mm	Depth (inches)	0.0028 inch
Height	25.4 mm	Height (inches)	1 inch
Width	19.1 mm	Width (inches)	0.752 inch
Net weight	0.11 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of printing	neutral	Width	19.1 mm
UL 94 flammability rating	V-0	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Colour	white
Halogen	Yes	Basic material	Vinyl film
Printed characters	without	Number per roll	5800

Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	12 mm ²
Conductor O.D., max.	4 mm	Conductor O.D., min.	2 mm
Cross-section for connected wire	12 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

THM WO-R VIN 25.4/19.1 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 76/360 SW	Version	
Order No.	2005080000	Ink ribbon	
GTIN (EAN)	4050118389951		
Qty.	1 ST		