


**THM WO-R VIN 25.4/57.2 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



**General ordering data**

|            |   |
|------------|---|
| Order No.  | 3062890000                                |
| Type       | <a href="#">THM WO-R VIN 25.4/57.2 WS</a> |
| GTIN (EAN) | 4099987049283                             |
| Qty.       | 2750 items                                |

**THM WO-R VIN 25.4/57.2 WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 0.07 mm | Depth (inches)  | 0.0028 inch |
| Height     | 25.4 mm | Height (inches) | 1 inch      |
| Width      | 57.2 mm | Width (inches)  | 2.252 inch  |
| Net weight | 0.32 g  |                 |             |

**General data**

|                                   |         |                                   |                |
|-----------------------------------|---------|-----------------------------------|----------------|
| Type of printing                  | neutral | Width                             | 57.2 mm        |
| UL 94 flammability rating         | V-0     | Operating temperature range, max. | 80 °C          |
| Operating temperature range, min. | -40 °C  | Colour                            | white          |
| Halogen                           | Yes     | Basic material                    | Vinyl film     |
| Printed characters                | without | Size of labelling field           | 19.1 x 25.4 mm |
| Number per roll                   | 2750    |                                   |                |

**Conductor and cable markers**

Halogen Yes

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |