

KLIPPON POK3 4M20AB CSS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**General ordering data**

Version	Housing with threaded hole, 75 x 160 x 56.5, Glass fibre-reinforced polyester, Drill holes side A: 4 x M20x1.5, Drill holes side B: 4 x M20x1.5
Order No.	8000004162
Type	KLIPPON POK3 4M20AB CSS
GTIN (EAN)	4032248986071
Qty.	1 items

KLIPPON POK3 4M20AB CSS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	56.5 mm	Depth (inches)	2.2244 inch
Height	75 mm	Height (inches)	2.9527 inch
Width	160 mm	Width (inches)	6.2992 inch
Net weight	428 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	c0b142f1-4049-4b95-bbc3-9959a2d3b09c

Material data

Surface finish	untreated, polished	Basic material	Glass fibre-reinforced polyester
----------------	---------------------	----------------	----------------------------------

General data

Colour	Silver grey	Protection degree	IP66, IP67
Colour chart (similar)	RAL 7001		

Assembly properties

Adjacent	No
----------	----

Housing

Basic material	Glass fibre-reinforced polyester	Assembled to fit rail	KL SET 18A4 S
Drill holes side C	none	Drill holes side D	none
Drill holes side A	4 x M20x1.5	Unassembled to fit rail	TS15_147 KLIPPON POK3 CSS
Drill holes side B	4 x M20x1.5		

Standard features

Reference product	KLIPPON POK 081606
-------------------	------------------------------------

Classifications



ETIM 8.0	EC000261	ETIM 9.0	EC000261
ETIM 10.0	EC000261	ECLASS 14.0	27-18-01-01
ECLASS 15.0	27-18-01-01		

KLIPPON POK3 4M20AB CSS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



KLIPPON POK3 4M20AB CSS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Plastic blanking plugs Ex e/i 7 Joule



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	VP M20 EX SI 7J	Version	
Order No.	2066730000	VPK EX 7J (Ex blanking plug, plastic, 7J), Blanking plug, in closed	
GTIN (EAN)	4050118415346	state, M 20, 11 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.),	
Qty.	100 ST	Polyamide 6	

KSG BN 0 NI - nickel-plated version with neoprene seal



The KSG is only intended for use when connecting non-armoured cables and lines. When the cable gland is ordered together with a neoprene seal, the seal allows temperatures from -35°C to +90°C. When using a silicone seal, a temperature range of -60°C to +180°C is possible. The O-ring and the cable gland included in the delivery are made from the same material. IP66 or IP68 protection at a depth of 25 metres under water (a pressure of 2.5 bar) is guaranteed when using this sealing material. The KSG is permitted for use with pressure-resistant Ex d encapsulations and increased safety Ex e.

General ordering data

Type	KSG M20 BN 0 NI 2 G20	Version	
Order No.	1911560000	KSG (Klippon standard Ex cable gland), Cable glands, straight, M 20,	
GTIN (EAN)	4032248539604	16 mm, OD min. 9.6 - OD max. 14 mm, ID min. 9.40 - ID max. 14.00	
Qty.	20 ST	mm, IP66, IP68 - 2.5 bar, Brass, nickel-plated	

External thread M20



ADAP series adaptors provide flexibility and versatility infilling unused entries in Ex equipment while maintaining Flameproof Ex d and Increased Safety Ex e explosion protection and IP66/67/68 ingress rate.

KLIPPON POK3 4M20AB CSS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

General ordering data

Type	ADAP EX M20-M16	Version	
Order No.	1737560000	ADAP (adaptor, extensions and reductions), Adapter, M 20 ,M 16,	
GTIN (EAN)	4008190957599	IP54, Brass, nickel-plated	
Qty.	1 ST		