

TS15X5 ST MPC1217 VER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



Similar to illustration

Accessories

General ordering data

| | |
|------------|---|
| Version | Rail, TS 15, Width: 4.13 mm, without slot, Steel, galvanized, chromium-plated |
| Order No. | 8000037598 |
| Type | TS15X5 ST MPC1217 VER |
| GTIN (EAN) | 4050118653106 |
| Qty. | 20 items |

TS15X5 ST MPC1217 VER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data
Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 5.5 mm | Depth (inches) | 0.2165 inch |
| Height | 0.59 mm | Height (inches) | 0.0232 inch |
| Width | 4.13 mm | Width (inches) | 0.1626 inch |
| Net weight | 18.28 g | | |

Temperatures

Operating temperature

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General information

| | | | |
|--------------------|--------------|---------------------|-----------------------------|
| Material thickness | 1 mm | Installation advice | Direct mounting |
| Standards | DIN EN 60715 | Surface finish | galvanized, chromium-plated |
| Basic material | Steel | Integral fixing | Screwed |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001285 | ETIM 9.0 | EC001285 |
| ETIM 10.0 | EC001285 | ECLASS 14.0 | 27-40-06-02 |
| ECLASS 15.0 | 27-40-06-02 | | |