

TS35X7.5 ST MPC1725 VER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



Similar to illustration

Accessories

General ordering data

| | |
|------------|--|
| Version | Rail, TS 35, TS 35 x 7.5, Width: 90 mm, without slot, Steel, galvanic zinc plated and passivated |
| Order No. | 8000037600 |
| Type | TS35X7.5 ST MPC1725 VER |
| GTIN (EAN) | 4050118653120 |
| Qty. | 20 items |

TS35X7.5 ST MPC1725 VER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data
Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 7.5 mm | Depth (inches) | 0.2953 inch |
| Height | 35 mm | Height (inches) | 1.378 inch |
| Width | 90 mm | Width (inches) | 3.5433 inch |
| Net weight | 57.5 g | | |

Temperatures

| | |
|-----------------------|--|
| Operating temperature | |
|-----------------------|--|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General information

| | | | |
|--------------------|-------------------------------------|----------------|--------------|
| Material thickness | 1 mm | Standards | DIN EN 60715 |
| Surface finish | galvanic zinc plated and passivated | Basic material | Steel |
| Integral fixing | Screwed | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001285 | ETIM 9.0 | EC001285 |
| ETIM 10.0 | EC001285 | ECLASS 14.0 | 27-40-06-02 |
| ECLASS 15.0 | 27-40-06-02 | | |