

TS15X5 ST FPC 20 VER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



Similar to illustration

Accessories

General ordering data

Version	Rail, TS 15, Width: 235 mm, without slot, Steel, galvanized, chromium-plated
Order No.	8000037604
Type	TS15X5 ST FPC 20 VER
GTIN (EAN)	4050118653168
Qty.	20 items

TS15X5 ST FPC 20 VER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	5.5 mm	Depth (inches)	0.2165 inch
Height	15 mm	Height (inches)	0.5906 inch
Width	235 mm	Width (inches)	9.252 inch
Net weight	28.96 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General information

Material thickness	1 mm	Installation advice	Direct mounting
Standards	DIN EN 60715	Surface finish	galvanized, chromium-plated
Basic material	Steel	Integral fixing	Screwed

Classifications

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		