

KEBXHS806020S4B1 AK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Klippon® EBx HS stainless steel enclosures, where the lid is fixed by Hinge and Screws, are offered as high quality products with leading performance characteristics in oil and chemistry hazardous industry. It is certified and complied with the international standards - like ATEX and IECEx approval.

General ordering data

| | |
|---------------|--|
| Version | Klippon EBx HS (Essential Box Ex - Hinge Screw), Empty enclosure, Height: 800 mm, Width: 600 mm, Depth: 200 mm, Gland plates: Bottom, Basic material: Stainless steel 1.4404 (316L), Brushed, silver |
| Order No. | 8000071030 |
| Type | KEBXHS806020S4B1 AK |
| GTIN (EAN) | 4064675385073 |
| Qty. | 1 items |
| Local product | Only available in certain countries |

KEBXHS806020S4B1 AK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

General ordering data

Local product Only available in certain countries

Dimensions and weights

| | | | |
|-----------------------------|---------|----------------------------|-------------|
| Depth | 200 mm | Depth (inches) | 7.874 inch |
| Height | 800 mm | Height (inches) | 31.496 inch |
| Width | 600 mm | Width (inches) | 23.622 inch |
| Mounting dimension - height | 760 mm | Mounting dimension - width | 560 mm |
| Net weight | 21735 g | | |

Temperatures

Operating temperature -55 °C...135 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Cable glands, left

| | | | |
|-----|-----|-----|-----|
| M63 | 8 | M75 | 7 |
| M12 | 392 | M50 | 20 |
| M16 | 195 | M32 | 48 |
| M25 | 82 | M20 | 130 |
| M40 | 25 | | |

Cable glands, right

| | | | |
|-----|-----|-----|-----|
| M25 | 82 | M63 | 8 |
| M75 | 7 | M16 | 195 |
| M40 | 25 | M50 | 20 |
| M32 | 48 | M20 | 130 |
| M12 | 392 | | |

Cable glands, top/bottom

| | | | |
|-----|-----|-----|-----|
| M20 | 74 | M12 | 217 |
| M63 | 6 | M40 | 18 |
| M32 | 22 | M25 | 44 |
| M50 | 7 | M75 | 5 |
| M16 | 115 | | |

KEBXHS806020S4B1 AK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Certificate numbers enclosure

| | | | |
|---|---------------------------|---|---------------------------|
| Declaration of Conformity No. (DoC LVD) | DE PS265X 210819 001ISS01 | Attestation of Conformity No. (AoC) | DE PS265x 210819 000ISS01 |
| Certificate no. empty enclosure (INMETRO) | LMP 21.0601U | Certificate no. Terminal Box (ATEX) | IBExU 21ATEX 1017 X |
| Certificate no. empty enclosure (ATEX) | IBExU 21ATEX 1016 U | Certificate no. Terminal Box (INMETRO) | LMP 21.0602X |
| Certificate no. Terminal Box (IECEX) | IECEX IBE 21.0012 | Certificate no. empty enclosure (IECEX) | IECEX IBE 21.0006U |
| Approval conditions | ATEX, IECEX, INMETRO | | |

General information

| | | | |
|-----------------------------|--|------------------------------|--|
| Material thickness of cover | 1.5 mm | Material thickness of flange | 3 mm |
| Material thickness | 1.5 mm | Operating temperature, max. | 135 °C |
| Operating temperature, min. | -55 °C | Lid attachment | M6 hex-head slotted screws SW10 + hinges |
| Standards | EN 60079-0, IEC 60079-0, EN 60079-7, IEC 60079-7, EN 60079-11, IEC 60079-11, EN 60079-31, IEC 60079-31 | Surface finish | Brushed |
| Impact resistance | 7 J ATEX version, 10 J version standard | AF size | 10 mm |
| Protection degree | IP66 | Basic material | Stainless steel 1.4404 (316L) |
| Seal material | Silicone (cover + flange) | Torque for lid screws | 2.5 Nm |
| Integral fixing | 4, 6 or 9 stud bolts M6 inner (female) thread | Enclosure attachment | 4 or 6, M6 blind thread hole on backside; optionally via additional mounting feet |
| Flange plate mounting | M6 hexagonal head screws 10 SW | Protection class (UL) | Type 1, Type 4, Type 4X |
| Number of lid screws | 4 | Gland plates | Bottom |
| Access opening: width | 543.6 mm | Opening angle lid | 125.00 ° |
| Flange plate | Yes | Max. payload | 49 kg |
| Lid | Yes | Access opening: height | 749.6 mm |
| Position PE bolts | Enclosure side C | Areas of use | Chemical industry, Explosive risk zone, Oil and gas industry, Onshore, Process industry, Building systems and technology, Machine construction, Packaging industry |

Housing earth

| | |
|----------------------------|--|
| Earth, enclosure, internal | Welded-on M6 stainless-steel earth stud in enclosure body and lid. |
|----------------------------|--|

horizontal assembly

| | | | |
|-----------------------------|------|-----------------|------|
| WDU 10 / ZDU 10 | 8x49 | WDU 16 / ZDU 16 | 8x41 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 8x98 | WDU 35 / ZDU 35 | 8x30 |
| WDU 4 / ZDU 4 | 8x82 | WDU 6 / ZDU 6 | 8x61 |

vertical assembly

| | | | |
|-----------------------------|-------|-----------------|------|
| WDU 10 / ZDU 10 | 6x69 | WDU 16 / ZDU 16 | 6x58 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 6x138 | WDU 35 / ZDU 35 | 6x43 |
| WDU 4 / ZDU 4 | 6x115 | WDU 6 / ZDU 6 | 6x86 |

KEBXHS806020S4B1 AK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Important note

Product information All articles with M6 threaded rivet as standard; UL variants with M10 earth bolt on request

Classifications


| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002503 | ETIM 9.0 | EC002503 |
| ETIM 10.0 | EC002503 | ECLASS 14.0 | 27-18-05-02 |
| ECLASS 15.0 | 27-18-05-02 | | |

KEBXHS806020S4B1 AK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



KEBXHS806020S4B1 AK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Mounting plates



Mounting plates, with and without hole patterns, for longitudinal and transverse mounting of DIN mounting rails or components directly onto the mounting plate.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | KEB MOPL 8060 MSZN | Version |
| Order No. | 8000074179 | Klippon EB (Essential Box), Mounting plate, Height: 740 mm, Width: |
| GTIN (EAN) | 4064675425243 | 540 mm, Depth: 12 mm, Basic material: Sheet steel, galvanized, silver |
| Qty. | 1 ST | |

| | | |
|------------|----------------------------|---|
| Type | KEB MOPL 8060 S2N H | Version |
| Order No. | 8000074325 | Klippon EB (Essential Box), Mounting plate, Height: 740 mm, Width: |
| GTIN (EAN) | 4064675425342 | 540 mm, Depth: 12 mm, Basic material: Stainless steel 1.4301 (304), |
| Qty. | 1 ST | untreated, silver |

Document holders



Document holders for the proper storage of documents in the enclosure.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | DOHA KEB A4 S4B R | Version |
| Order No. | 8000075809 | Klippon EB (Essential Box), Enclosures, Riveted, Height: 175 mm, |
| GTIN (EAN) | 4064675425656 | Depth: 20 mm, Basic material: Stainless steel 1.4404, silver |
| Qty. | 1 ST | |

| | | |
|------------|----------------------------|--|
| Type | DOHA KEB A5 S4B R | Version |
| Order No. | 8000075808 | Klippon EB (Essential Box), Enclosures, Riveted, Height: 125 mm, |
| GTIN (EAN) | 4064675425649 | Depth: 20 mm, Basic material: Stainless steel 1.4404, silver |
| Qty. | 1 ST | |

| | | |
|------------|----------------------------|---|
| Type | DOHA KEB A6 S4B R | Version |
| Order No. | 8000075807 | Klippon EB (Essential Box), Enclosures, Riveted, Height: 95 mm, |
| GTIN (EAN) | 4064675425359 | Depth: 20 mm, Basic material: Stainless steel 1.4404, silver |
| Qty. | 1 ST | |

KEBXHS806020S4B1 AK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Mounting feet



With the additionally available mounting feet, the enclosures can also be mounted from outside the enclosure.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | KEB MOFT SMALL S4 SET | Version |
| Order No. | 2660200318 | Klippon EB (Essential Box), Mounting foot, Height: 38 mm, Width: 55 |
| GTIN (EAN) | 4064675275695 | mm, Depth: 10.5 mm, Basic material: Steel, untreated, silver |
| Qty. | 1 ST | |

Spacer



Stainless steel spacers in three lengths to increase the distance between the mounting rails or DIN rails and the rear wall of the enclosure.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SP M6 15 MSZN | Version |
| Order No. | 3896100000 | Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm, |
| GTIN (EAN) | 4008190857851 | Depth: 15 mm, Basic material: Steel, silver |
| Qty. | 2 ST | |
| Type | SP M6 20 MSZN | Version |
| Order No. | 3896200000 | Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm, |
| GTIN (EAN) | 4008190850234 | Depth: 20 mm, Basic material: Steel, silver |
| Qty. | 2 ST | |
| Type | SP M6 30 MSZN | Version |
| Order No. | 3896300000 | Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm, |
| GTIN (EAN) | 4008190850241 | Depth: 30 mm, Basic material: Steel, silver |
| Qty. | 2 ST | |

KEBXHS806020S4B1 AK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type label holder



There are a variety of designed label holders available for prominent display as required and for additional nameplates as needed.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | TPSDHA KEB 100X25 S4B R | Version |
| Order No. | 8000075818 | Klippon EB (Essential Box), Enclosures, Riveted, Height: 25 mm, |
| GTIN (EAN) | 4064675425632 | Width: 141 mm, Depth: 16.5 mm, Basic material: Stainless steel |
| Qty. | 1 ST | 1.4404 (316L), Brushed, silver |

| | | |
|------------|----------------------------|---|
| Type | TPSDHA KEB 130X50 S4B R | Version |
| Order No. | 8000075816 | Klippon EB (Essential Box), Enclosures, Riveted, Height: 50 mm, |
| GTIN (EAN) | 4064675425366 | Width: 171 mm, Depth: 16.5 mm, Basic material: Stainless steel |
| Qty. | 1 ST | 1.4404 (316L), Brushed, silver |

Mounting plates



Mounting plates, with and without hole patterns, for longitudinal and transverse mounting of DIN mounting rails or components directly onto the mounting plate.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | GFSC M5X10 TX20 SET | Version |
| Order No. | 1274150000 | Klippon EB (Essential Box), Mounting screw, Height: 13.3 mm, Width: |
| GTIN (EAN) | 4050118063820 | 8.5 mm, Depth: 8.5 mm, Basic material: Steel, galvanized, galvanic |
| Qty. | 1 ST | zinc plated and passivated, silver |

KEBXHS806020S4B1 AK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Installation material



Integrate, expand and customise - the perfect supplement to every application

The fully structured range of system accessories for the new Klippon® TB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

Mounting hardware kits

Mounting hardware kits are available for quick and easy installation of type label holders, document holders and rain hoods.

The label fastening set – SD is required to install a plastic (Trafolyte) ID or type label. With the aid of this set can you mount the ID or type label directly on the enclosure cover. The label fastening set has been specially developed for this purpose. Only by using this fastening set can you ensure that there will be no leaks into the enclosure or damage to the label.

The universal fastening set – TPSD has been developed to enable secure and quick installation of type label holders, rain covers or document holders, for example. By using this fastening set, the risk of leaks can be minimised, if not avoided.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | LKSC M6X8 A2 TX30 | Version | |
| Order No. | 2704960000 | Klippon TB (Terminal Box), Set of fixings, Height: 11.3 mm, Width: 13.6 mm, Depth: 13.6 mm, Basic material: Stainless steel, rust-proof, untreated, silver | |
| GTIN (EAN) | 4050118753196 | | |
| Qty. | 500 ST | | |

Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | SDIS SLIM 1.2X6.5X150 | Version | |
| Order No. | 2749640000 | Mounting tool, Blade width (B): 6.5 mm, Blade length: 150 mm, Blade thickness (A): 1.2 mm | |
| GTIN (EAN) | 4050118896381 | | |
| Qty. | 1 ST | | |