

KEBIQL806020S2NO AL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**General ordering data**

| | |
|------------|--|
| Version | Klippon EBi QL (Essential Box industrial - Quarter Lock), Enclosures, Height: 800 mm, Width: 600 mm, Depth: 200 mm, Basic material: Stainless steel 1.4301 (304), Brushed, untreated, silver |
| Order No. | 8000133643 |
| Type | KEBIQL806020S2NO AL |
| GTIN (EAN) | 4099987368568 |
| Qty. | 1 items |

KEBIQL806020S2N0 AL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



Dimensions and weights

| | | | |
|------------|------------|-----------------|-------------|
| Depth | 200 mm | Depth (inches) | 7.874 inch |
| Height | 800 mm | Height (inches) | 31.496 inch |
| Width | 600 mm | Width (inches) | 23.622 inch |
| Net weight | 19768.26 g | | |

Temperatures

Operating temperature -40 °C...85 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Cable glands, right

| | | | |
|-----|----|-----|-----|
| M25 | 51 | M63 | 7 |
| M16 | 84 | M40 | 22 |
| M50 | 8 | M32 | 28 |
| M20 | 80 | M12 | 192 |

Cable glands, top/bottom

| | | | |
|-----|----|-----|-----|
| M20 | 42 | M12 | 138 |
| M63 | 5 | M40 | 16 |
| M32 | 20 | M25 | 24 |
| M50 | 6 | M16 | 45 |

Certificate numbers enclosure

| | | | |
|---|---------------------------|---------------------|----|
| Declaration of Conformity No. (DoC LVD) | DE PS2650 220428 001ISS01 | Approval conditions | CE |
|---|---------------------------|---------------------|----|

General information

| | | | |
|-----------------------------|---|---------------------------------|---------------------------------|
| Material thickness of cover | 1.5 mm | Material thickness of enclosure | 1.5 mm |
| Material thickness | 1.5 mm | Operating temperature, max. | 85 °C |
| Operating temperature, min. | -40 °C | Surface finish | Brushed, untreated |
| Impact resistance | 10 J version standard | Protection degree | IP66 |
| Basic material | Stainless steel 1.4301 (304) | Seal material | Polyurethane |
| Enclosure attachment | 4 or 6, M6 blind thread hole on backside; optionally via additional mounting feet | Flange plate | No |
| Lid | Yes | Areas of use | Building systems and technology |

KEBIQL806020S2N0 AL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Housing earth

| | | | |
|----------------------------|--|----------------------------|--|
| Earth, enclosure, cover | Welded-on M6 stainless-steel earth stud in enclosure body and lid. | Earth, enclosure, external | Welded-on M6 stainless-steel earth stud in enclosure body and lid. |
| Earth, enclosure, internal | Welded-on M6 stainless-steel earth stud in enclosure body and lid. | | |

horizontal assembly

| | | | |
|-----------------------------|------|-----------------|------|
| WDU 10 / ZDU 10 | 4x51 | WDU 16 / ZDU 16 | 3x44 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 4x98 | WDU 35 / ZDU 35 | 2x31 |
| WDU 4 / ZDU 4 | 4x83 | WDU 6 / ZDU 6 | 4x64 |

vertical assembly

| | | | |
|-----------------------------|-------|-----------------|------|
| WDU 10 / ZDU 10 | 4x70 | WDU 16 / ZDU 16 | 3x61 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 5x132 | WDU 35 / ZDU 35 | 2x44 |
| WDU 4 / ZDU 4 | 4x111 | WDU 6 / ZDU 6 | 4x94 |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000261 | ETIM 9.0 | EC000261 |
| ETIM 10.0 | EC000261 | ECLASS 14.0 | 27-18-01-01 |
| ECLASS 15.0 | 27-18-01-01 | | |

KEBIQL806020S2N0 AL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Document holders

Document holders for the proper storage of documents in the enclosure.



General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | DOHA KEB A4 S4B R | Version | |
| Order No. | 8000075809 | Klippon EB (Essential Box), Enclosures, Riveted, Height: 175 mm, | |
| GTIN (EAN) | 4064675425656 | Depth: 20 mm, Basic material: Stainless steel 1.4404, silver | |
| Qty. | 1 ST | | |
| Type | DOHA KEB A5 S4B R | Version | |
| Order No. | 8000075808 | Klippon EB (Essential Box), Enclosures, Riveted, Height: 125 mm, | |
| GTIN (EAN) | 4064675425649 | Depth: 20 mm, Basic material: Stainless steel 1.4404, silver | |
| Qty. | 1 ST | | |
| Type | DOHA KEB A6 S4B R | Version | |
| Order No. | 8000075807 | Klippon EB (Essential Box), Enclosures, Riveted, Height: 95 mm, | |
| GTIN (EAN) | 4064675425359 | Depth: 20 mm, Basic material: Stainless steel 1.4404, silver | |
| Qty. | 1 ST | | |

Mounting feet

With the additionally available mounting feet, the enclosures can also be mounted from outside the enclosure.



General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | KEB MOFT SMALL S4 SET | Version | |
| Order No. | 2660200318 | Klippon EB (Essential Box), Mounting foot, Height: 38 mm, Width: 55 mm, Depth: 10.5 mm, Basic material: Steel, untreated, silver | |
| GTIN (EAN) | 4064675275695 | | |
| Qty. | 1 ST | | |

KEBIQL806020S2N0 AL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Spacer



Stainless steel spacers in three lengths to increase the distance between the mounting rails or DIN rails and the rear wall of the enclosure.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SP M6 15 MSZN | Version |
| Order No. | 3896100000 | Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm, |
| GTIN (EAN) | 4008190857851 | Depth: 15 mm, Basic material: Steel, silver |
| Qty. | 2 ST | |
| Type | SP M6 20 MSZN | Version |
| Order No. | 3896200000 | Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm, |
| GTIN (EAN) | 4008190850234 | Depth: 20 mm, Basic material: Steel, silver |
| Qty. | 2 ST | |
| Type | SP M6 30 MSZN | Version |
| Order No. | 3896300000 | Klippon EB (Essential Box), Spacer, Height: 11.2 mm, Width: 10 mm, |
| GTIN (EAN) | 4008190850241 | Depth: 30 mm, Basic material: Steel, silver |
| Qty. | 2 ST | |

Type label holder



There are a variety of designed label holders available for prominent display as required and for additional nameplates as needed.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | TPSDHA KEB 100X25 S4B R | Version |
| Order No. | 8000075818 | Klippon EB (Essential Box), Enclosures, Riveted, Height: 25 mm, |
| GTIN (EAN) | 4064675425632 | Width: 141 mm, Depth: 16.5 mm, Basic material: Stainless steel |
| Qty. | 1 ST | 1.4404 (316L), Brushed, silver |
| Type | TPSDHA KEB 130X50 S4B R | Version |
| Order No. | 8000075816 | Klippon EB (Essential Box), Enclosures, Riveted, Height: 50 mm, |
| GTIN (EAN) | 4064675425366 | Width: 171 mm, Depth: 16.5 mm, Basic material: Stainless steel |
| Qty. | 1 ST | 1.4404 (316L), Brushed, silver |

KEBIQL806020S2N0 AL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Mounting plates



Mounting plates, with and without hole patterns, for longitudinal and transverse mounting of DIN mounting rails or components directly onto the mounting plate.

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | GFSC M5X10 TX20 SET | Version | |
| Order No. | 1274150000 | Klippon EB (Essential Box), Mounting screw, Height: 13.3 mm, Width: 8.5 mm, Depth: 8.5 mm, Basic material: Steel, galvanized, galvanic zinc plated and passivated, silver | |
| GTIN (EAN) | 4050118063820 | | |
| Qty. | 1 ST | | |

Installation material



Integrate, expand and customise - the perfect supplement to every application

The fully structured range of system accessories for the new Klippon® TB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

Mounting hardware kits

Mounting hardware kits are available for quick and easy installation of type label holders, document holders and rain hoods.

The label fastening set – SD is required to install a plastic (Trafolyte) ID or type label. With the aid of this set can you mount the ID or type label directly on the enclosure cover. The label fastening set has been specially developed for this purpose. Only by using this fastening set can you ensure that there will be no leaks into the enclosure or damage to the label.

The universal fastening set – TPSD has been developed to enable secure and quick installation of type label holders, rain covers or document holders, for example. By using this fastening set, the risk of leaks can be minimised, if not avoided.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | LKSC M6X8 A2 TX30 | Version | |
| Order No. | 2704960000 | Klippon TB (Terminal Box), Set of fixings, Height: 11.3 mm, Width: 13.6 mm, Depth: 13.6 mm, Basic material: Stainless steel, rust-proof, untreated, silver | |
| GTIN (EAN) | 4050118753196 | | |
| Qty. | 500 ST | | |


KEBIQL806020S2N0 AL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | SDIS SLIM 1.2X6.5X150 | Version | |
| Order No. | 2749640000 | Mounting tool, Blade width (B): 6.5 mm, Blade length: 150 mm, Blade thickness (A): 1.2 mm | |
| GTIN (EAN) | 4050118896381 | | |
| Qty. | 1 ST | | |

Mounting plates



Mounting plates, with and without hole patterns, for longitudinal and transverse mounting of DIN mounting rails or components directly onto the mounting plate.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | KEB MOPL 8060 S2N H | Version | |
| Order No. | 8000074325 | Klippon EB (Essential Box), Mounting plate, Height: 740 mm, Width: 540 mm, Depth: 12 mm, Basic material: Stainless steel 1.4301 (304), untreated, silver | |
| GTIN (EAN) | 4064675425342 | | |
| Qty. | 1 ST | | |
| Type | KEB MOPL 8060 MSZN | Version | |
| Order No. | 8000074179 | Klippon EB (Essential Box), Mounting plate, Height: 740 mm, Width: 540 mm, Depth: 12 mm, Basic material: Sheet steel, galvanized, silver | |
| GTIN (EAN) | 4064675425243 | | |
| Qty. | 1 ST | | |

Double-bit key



With the double-bit key, the locking element of the enclosure door can be locked and opened.

KEBIQL806020S2N0 AL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | KLIPPON QL KEY | Version | |
| Order No. | 2473930000 | Klippon EB (Essential Box), Key, Miscellaneous, Basic material: Plastic | |
| GTIN (EAN) | 4050118485868 | | |
| Qty. | 5 ST | | |