

SCHUKO TS35

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- Simple installation in electrical cabinet
- TS35 module can be mounted on rail
- VDE mark of conformity
- Two-pole with earthing contact

General ordering data

Version	Electrical-cabinet socket outlet TS 35
Order No.	8734580000
Type	SCHUKO TS35
GTIN (EAN)	4032248407835
Qty.	10 items
Delivery status	This article will no longer be available in the future.
Available until	2024-08-03T00:00:00+02:00

SCHUKO TS35

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Height	45 mm	Height (inches)	1.7716 inch
Width	76 mm	Width (inches)	2.9921 inch
Length	60 mm	Length (inches)	2.3622 inch
Net weight	95 g		

Temperatures

Storage temperature -20 °C...40 °C Operating temperature -20 °C...40

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Input

Nominal current 16 A

General data

Surge voltage category II

Insulation coordination

Surge voltage category II Pollution severity 2

General data

Design Installation housing Colour beige
 Mounting rail TS 35

Insulation coordination acc. to EN 50178

Surge voltage category II Pollution severity 2

Classifications

ETIM 8.0	EC000125	ETIM 9.0	EC000125
ETIM 10.0	EC000125	ECLASS 14.0	27-14-40-42
ECLASS 15.0	27-14-40-42		

SCHUKO TS35


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type	WEW 35/1 V0 GF SW	Version	
Order No.	1478990000	End bracket, black, TS 35, V-0, Wemid, Width: 12 mm, 130 °C	
GTIN (EAN)	4050118286892		
Qty.	50 ST		
Type	WEW 35/2 V0 GF SW	Version	
Order No.	1479000000	End bracket, black, TS 35, V-0, Wemid, Width: 8 mm, 130 °C	
GTIN (EAN)	4050118286779		
Qty.	50 ST		

Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Type	SDIS SL 0.6X3.5X100	Version	
Order No.	1274660000	Screwdriver, Mounting tool	
GTIN (EAN)	4050118072631		
Qty.	1 ST		

Crosshead screwdriver, Pozidrive



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

Accessories

General ordering data

Type	SDIK PZ1 SL	Version	
Order No.	1274730000	Screwdriver, Screwdriver	
GTIN (EAN)	4050118073225		
Qty.	1 ST		