

IE-P-IP67

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



SnapIn plug-in connectors according to IEC 61076-3-106
ver.6 in plastic, with RJ45 insert

General ordering data

Version	Connecting plug, Plug, IP67, Cat.6A / Class EA (ISO/IEC 11801 2010), Variant 6 to IEC 61076-3-106
Order No.	8808380000
Type	IE-P-IP67
GTIN (EAN)	4032248505968
Qty.	1 items

IE-P-IP67

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 29 g

Temperatures

Storage temperature Installation temperature Operating temperature -40 °C...70 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Connection 1	RJ45	Connection 2	IDC
Description of article	Plug	Wiring	EIA/TIA T568 A
Colour	Light Grey	Housing main material	PA 66, UL 94: V-0
Category	Cat.6A / Class EA (ISO/ IEC 11801 2010)	Contact surface	Gold over nickel
Type of mounting	Floor-mounted, for exposed connections, Wall mounting	Shielding	360°; shield contact
Protection degree	IP67	Plugging cycles	750


General standards

Certificate No. (DNV) TAE00003EW Connector standard IEC 61076-3-106 Var. 6, IEC 60603-7-5

Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

Dimensioned drawing



IE-P-IP67

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

... for modular plug-in connectors



Crimping tools for modular plug-in connector systems WE and DEC

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- Three functions in one tool

General ordering data

Type	TT 8 RS MP 8	Version	
Order No.	9202800000	Pressing tools, Crimping tool for contacts	
GTIN (EAN)	4032248512072		
Qty.	1 ST		

RJ45 crimp

RJ45 crimp plug-in connector according to IEC 60603-7-51 for wire outer diameters up to 1.05 mm



General ordering data

Type	IE-PM-RJ45-TH	Version	
Order No.	1963580000	RJ45 crimp plug, Plug without bending protection sleeve, Cat.6A /	
GTIN (EAN)	4032248645688	Class EA (ISO/IEC 11801 2010)	
Qty.	100 ST		

IE-P-IP67

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Counterpart

www.weidmueller.com

Sets - RJ45

SnapIn plug-in connectors according to IEC 61076-3-106 ver.6 in plastic, with RJ45 insert



General ordering data

Type	IE-XM-6D-RJ45/RJ45-IP67	Version
Order No.	8829450000	Mounting flange, Coupling flange, 90° down, Cat.6 (ISO/IEC 11801), IP67
GTIN (EAN)	4032248532476	
Qty.	1 ST	
Type	IE-XM-6U-RJ45/RJ45-IP67	Version
Order No.	8829440000	Mounting flange, Coupling flange, 90° up, Cat.6 (ISO/IEC 11801), IP67
GTIN (EAN)	4032248532469	
Qty.	1 ST	
Type	IE-XM-RJ45/IDC-IP67	Version
Order No.	8808440000	Mounting flange, RJ45 module flange, straight, Cat.6A / Class EA (ISO/IEC 11801 2010), IP67
GTIN (EAN)	4032248506026	
Qty.	1 ST	
Type	IE-XM-RJ45/RJ45-IP67	Version
Order No.	8808450000	Mounting flange, Coupling flange, straight, Cat.6A / Class EA (ISO/IEC 11801 2010), IP67
GTIN (EAN)	4032248506033	
Qty.	1 ST	