

## IE-C-IP67

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



SnapIn plug-in connectors according to IEC 61076-3-106 ver.6 in plastic, with RJ45 insert

### General ordering data

Version	Connecting plug, Cable coupling, IP67, Cat.6A / Class EA (ISO/IEC 11801 2010), Variant 6 to IEC 61076-3-106
Order No.	<a href="#">8813090000</a>
Type	IE-C-IP67
GTIN (EAN)	4032248512843
Qty.	1 items

## IE-C-IP67

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Net weight 66.88 g

## Temperatures

Storage temperature Operating temperature -40 °C...70 °C

Installation temperature

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

## General data

Connection 1	RJ45	Connection 2	IDC
Description of article	Cable coupling	Composition	Coupling including RJ 45 module with IDC connection
Wiring	Colour-coded pin assignment according to EIA/TIA T568 A., EIA/TIA T568 B	Colour	Light Grey
Housing main material	PA 66, UL 94: V-0	Category	Cat.6A / Class EA (ISO/IEC 11801 2010)
Contact surface	Gold over nickel	Sheath diameter, min.	6 mm
Sheath diameter, max.	9.5 mm	Type of mounting	Floor-mounted, for exposed connections, Wall mounting
Shielding	360° shield contact	Protection degree	IP67
Plugging cycles	750		

## General standards

Certificate No. (DNV) TAE00003EW Connector standard IEC 61076-3-106 Var. 6, IEC 60603-7-5

## Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

**IE-C-IP67**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

**Dimensioned drawing**

