


H10,0/24,0X R SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- Polypropylene conical cable entry
 - Heat-resistant up to 105°C
- for conductors from 1.5 to 16 mm² (AWG 16-6)
tin-plated copper
dimensional tolerances to DIN 46228 part 4

General ordering data

Version	Wire-end ferrule, Standard, 17 mm, 12 mm, red
Order No.	9006830000
Type	H10,0/24,0X R SV
GTIN (EAN)	4008 190332310
Qty.	100 items
Packaging	Multipack bag

H10,0/24,0X R SV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 0.64 g

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Technical data

Description of article	Wire end ferrule for short-circuit-proof and earth-fault-proof lines, red	Version	Standard

Wire-end ferrules

Contact surface diameter (D1)	4.6 mm	Contact surface length (L2)	12 mm
Collar diameter (D2)	9.8 mm	Plastic collar thickness (S2)	0.3 mm
L1 in mm	24.00 mm	Wire connection cross section AWG, max.	AWG 8
Metal sleeve thickness (S1)	0.2 mm	Stripping length	17 mm
Conductor cross-section	10 mm ²	Colour code	Weidmueller

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawing

