

HTF RSV 12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Crimping tools for Weidmüller contacts for RSV and DSTV-HD systems

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

General ordering data

Version	Pressing tool, Crimping tool for contacts, Foder-Bcrimp
Order No.	9013550000
Type	HTF RSV 12
GTIN (EAN)	4008 190002046
Qty.	1 items

HTF RSV 12

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	205 mm	Width (inches)	8.0709 inch
Net weight	449.98 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	Crimping tools for Weidmüller RSV and DSTV-HD contacts, AWG 14-12	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

Description of contact

Type of contact	RSV and DSTV-HD	Conductor cross-section, max. AWG	AWG 12
Conductor cross-section, min. AWG	AWG 14		

tool data crimping

Wire end ferrules cross-section, max.	4 mm ²	Crimping type/profile	FoderBcrimp
---------------------------------------	-------------------	-----------------------	-------------

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

Drawings

