


H95,0/44 R

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

Version	Wire-end ferrule, Standard, 31 mm, 25 mm, red
Order No.	9028210000
Type	H95,0/44 R
GTIN (EAN)	4008190891589
Qty.	25 items
Packaging	loose

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Dimensions and weights

Net weight	5.2 g
------------	-------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Wire end ferrule with plastic collar, red	Version	Standard
------------------------	-------------------------------------------	---------	----------

Wire-end ferrules

Contact surface diameter (D1)	14.7 mm	Contact surface length (L2)	25 mm
Collar diameter (D2)	18 mm	Plastic collar thickness (S2)	0.6 mm
L1 in mm	44.00 mm	Wire connection cross section AWG, max.	AWG 3/0
Metal sleeve thickness (S1)	0.35 mm	Stripping length	31 mm
Conductor cross-section	95 mm ²	Colour code	Weidmueller

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawing

