

## H1,5/24 XS SW

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- In multi-pack bag
- Weidmüller colour code

### General ordering data

Version	Wire-end ferrule, Standard, 18 mm, 14.5 mm, black
Order No.	<a href="#">9202870000</a>
Type	H1,5/24 XS SW
GTIN (EAN)	4032248517947
Qty.	100 items
Packaging	loose

**H1,5/24 XS SW**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 0.26 g

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Technical data**

Description of article	Wire end ferrule for short-circuit-proof and earth-fault-proof lines, black	Version	Standard

**Wire-end ferrules**

Contact surface diameter (D1)	1.8 mm	Contact surface length (L2)	14.5 mm
Collar diameter (D2)	7 mm	Plastic collar thickness (S2)	0.3 mm
L1 in mm	24.00 mm	Wire connection cross section AWG, max.	AWG 16
Metal sleeve thickness (S1)	0.15 mm	Stripping length	18 mm
Conductor cross-section	1.5 mm <sup>2</sup>	Colour code	Weidmueller

**Classifications**

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Drawing

