

MPC 17/17/15 TRSP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Small and medium-sized polycarbonate enclosures

The polycarbonate enclosures of the MPC series are ideal for building into electrical, electromechanical and pneumatic devices as well as PCBs. The enclosures are used in situations with extreme mechanical and chemical conditions.

Features:

- 17 sizes in 2 versions
- Grey or transparent cover
- Cover with lead-seal holes
- Mounting holes outside the seal area
- Receptacle threads for rail mounting, mounting plates and circuit board
- Comprehensive accessories
- Weidmüller can manufacture and supply the enclosure to match customer specifications, fitted with all necessary terminals and cable glands.

General ordering data

| | |
|------------|---|
| Version | MPC (polycarbonate empty enclosure), Empty enclosure, Height: 175 mm, Width: 175 mm, Depth: 150 mm, Basic material: Polycarbonate, untreated, Light Grey, Transparent |
| Order No. | 9535440000 |
| Type | MPC 17/17/15 TRSP |
| GTIN (EAN) | 4032248016815 |
| Qty. | 1 items |

MPC 17/17/15 TRSP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 150 mm | Depth (inches) | 5.9055 inch |
| Height | 175 mm | Height (inches) | 6.8898 inch |
| Width | 175 mm | Width (inches) | 6.8898 inch |
| Net weight | 180 g | | |

Temperatures

| | |
|-----------------------|-----------------|
| Operating temperature | -50 °C...130 °C |
|-----------------------|-----------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Cable glands, right

| | | | |
|-----|---|-----|---|
| M16 | 4 | M12 | 6 |
|-----|---|-----|---|

Cable glands, top/bottom

| | | | |
|-----|---|-----|---|
| M20 | 4 | M12 | 6 |
| M16 | 4 | | |

Certificate numbers enclosure

| | |
|---|----------------------------------|
| Declaration of Conformity No. (DoC LVD) | DoC DE PS2420 201008 001ISS00 |
|---|----------------------------------|

General information

| | | | |
|-----------------------------|---|-----------------------------|-------------------------------|
| Material thickness | 3.5 mm | Operating temperature, max. | 130 °C |
| Operating temperature, min. | -50 °C | Lid attachment | 4 polyamide crosshead screws |
| Installation advice | Screw mounting | Surface finish | untreated |
| Impact resistance | IK08 | Protection degree | IP66, IP67 |
| Basic material | Polycarbonate | Seal material | Polyurethane |
| Torque for lid screws | 0.8 Nm | Integral fixing | thanks to self-tapping screws |
| Enclosure attachment | Holes 4.5 mm | Number of lid screws | 4 |
| Access opening: width | 171.5 mm | Flange plate | No |
| Lid | Yes | Access opening: height | 171.5 mm |
| Areas of use | Building systems and technology, Transportation, Packaging industry, Machine construction | | |

horizontal assembly

| | | | |
|-----------------------------|------|-----------------|------|
| WDU 10 / ZDU 10 | 1x11 | WDU 16 / ZDU 16 | 1x9 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 1x22 | WDU 35 / ZDU 35 | 1x7 |
| WDU 4 / ZDU 4 | 1x19 | WDU 6 / ZDU 6 | 1x14 |

MPC 17/17/15 TRSP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**vertical assembly**

| | | | |
|-----------------------------|------|-----------------|------|
| WDU 10 / ZDU 10 | 1x11 | WDU 16 / ZDU 16 | 1x9 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 1x22 | WDU 35 / ZDU 35 | 1x7 |
| WDU 4 / ZDU 4 | 1x19 | WDU 6 / ZDU 6 | 1x14 |

Classifications


| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000261 | ETIM 9.0 | EC000261 |
| ETIM 10.0 | EC000261 | ECLASS 14.0 | 27-18-01-01 |
| ECLASS 15.0 | 27-18-01-01 | | |

MPC 17/17/15 TRSP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



MPC 17/17/15 TRSP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Fixing Material



Accessories

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | SC MPC | Version | |
| Order No. | 9535640000 | MPC (polycarbonate empty enclosure), Mounting screw, Screws, | |
| GTIN (EAN) | 4032248009428 | Height: 12.5 mm, Width: 7 mm, Depth: 12.5 mm, Basic material: | |
| Qty. | 100 ST | Steel, galvanised | |

Hinge



MPC series, hinges, set of 2

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | HG MPC | Version | |
| Order No. | 9535590000 | MPC (polycarbonate empty enclosure), External joint, Hinge, Basic | |
| GTIN (EAN) | 4032248009329 | material: Plastic | |
| Qty. | 1 ST | | |

External fixing lugs



External attachment lugs 4-part set

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | MF MPC | Version | |
| Order No. | 9535600000 | MPC (polycarbonate empty enclosure), Mounting foot, Fixing lugs, | |
| GTIN (EAN) | 4032248009381 | Height: 30 mm, Width: 15 mm, Depth: 10 mm, Basic material: Plastic | |
| Qty. | 1 ST | | |

MPC 17/17/15 TRSP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Klippon® POK earthing stud



The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | PEBZ M10 S4 SET | Version |
| Order No. | 1283440000 | Klippon POK (polyester empty enclosure), Earthing stud, |
| GTIN (EAN) | 4050118073362 | Miscellaneous, Height: 21 mm, Width: 21 mm, Depth: 48.7 mm, |
| Qty. | 1 ST | Basic material: Stainless steel 1.4404 (316L) |

Earthing stud



Earthing bolts to exchange as a complete component in two versions – brass and stainless steel.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | PEBZ M10 BR SET | Version |
| Order No. | 1277220000 | Klippon POK (polyester empty enclosure), Earthing stud, |
| GTIN (EAN) | 4050118067019 | Miscellaneous, Height: 21 mm, Width: 21 mm, Depth: 48.7 mm, |
| Qty. | 1 ST | Basic material: Brass |

Klippon® POK earthing stud



The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | PEBZ M6 BR SET | Version |
| Order No. | 1277250000 | Klippon POK (polyester empty enclosure), Earthing stud, |
| GTIN (EAN) | 4050118067149 | Miscellaneous, Height: 12.3 mm, Width: 12.3 mm, Depth: 42 mm, |
| Qty. | 1 ST | Basic material: Brass |

Earthing stud

Accessories



General ordering data

| | | |
|------------|----------------------------|---|
| Type | PEBZ M6 S4 SET | Version |
| Order No. | 1283430000 | Klippon POK (polyester empty enclosure), Earthing stud, |
| GTIN (EAN) | 4050118073607 | Miscellaneous, Height: 12.3 mm, Width: 12.3 mm, Depth: 42 mm, |
| Qty. | 1 ST | Basic material: Stainless steel 1.4404 (316L) |

MPC 17/17/15 TRSP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Mounting support



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | FKSC M4X6 D8/SW2 | Version | |
| Order No. | 1567480000 | SAK Series, Allen hex screw, Screws, Number of poles: 1 | |
| GTIN (EAN) | 4008190033491 | | |
| Qty. | 100 ST | | |

Ventilation plugs - DAE



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | DAE M12 SS | Version | |
| Order No. | 1868550000 | DAE (ventilation element), Compensating element, straight, M 12, 10 mm, IP66, IP68, IP69K, Stainless steel 1.4305 (303) | |
| GTIN (EAN) | 4032248440405 | | |
| Qty. | 10 ST | | |
| Type | DAE M12 PA LONG | Version | |
| Order No. | 1868570000 | DAE (ventilation element), Compensating element, straight, M 12, 10 mm, IP66, IP68, IP69K, Polyamide 6 | |
| GTIN (EAN) | 4032248440429 | | |
| Qty. | 10 ST | | |

MPC

Mounting plates, 1.5 mm sheet steel, galvanised



MPC 17/17/15 TRSP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | MP MPC 17/17 | Version | |
| Order No. | 9535570000 | MPC (polycarbonate empty enclosure), Mounting plate, Mounting | |
| GTIN (EAN) | 4032248009305 | plate, Height: 148 mm, Width: 148 mm, Depth: 1.5 mm, Basic | |
| Qty. | 1 ST | material: Sheet steel, galvanized, galvanized | |

TS 35

Accessories



General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | TS35X7.5 ST MPC1725 VER | Version | |
| Order No. | 8000037600 | Rail, TS 35, TS 35 x 7.5, Width: 90 mm, without slot, Steel, galvanic | |
| GTIN (EAN) | 4050118653120 | zinc plated and passivated | |
| Qty. | 20 ST | | |