数据信息页

U-LINK-EC-10-CONNECTION-1Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

应用举例



The Weidmüller u-link Remote Access Service in easyConnect offers an easy way to securely access Ethernet devices in remote networks.
With the u-link VPN Server as the central meeting point server, the VPN clients (service PC, Weidmüller u-link client devices and Third-Party OpenVPN capable devices) always connect outbound and thus conform to typical IT security requirements.
Separate database and server instances are used for each customer account (secure client isolation) to ensure data integrity.
Communication between the u-link VPN server and remote clients (service PCs and u-link client devices) takes place via a certificate-protected OpenVPN connection.
The u-link principle is "configuration instead of programming". The use is intuitive and does not require expert knowledge.
Featureset:

- 1-click VPN remote access for service PCs
- Web Access: web connections to remote hosts fully browser-based for use with tablets or smartphones
- Organization and Group Management
- Topologies including third-party end devices
- Firmware management: display of the firmware status of all Weidmüller devices and the option of time-controlled, automated firmware updates
- Individual access rights: granular configuration of access rights to devices in the target network
- Extensive event log: overview of activities with comprehensive filter and export functions

With u-link Remote Access integrated into easyConnect, Weidmüller offers a scalable licensing concept based on the number and type of connected devices as well as the required number of simultaneous VPN connections.
Weidmüller device licenses:

- Available for up to 50, 100, 250, 500, 750 or 1000 Weidmüller devices
- Provides secure remote access to the corresponding number of Weidmüller devices through easyConnect
- License validity: 1 year

Third-party devices via OpenVPN:

- Available for up to 600, 1200 or 1800 third-party devices
- Enables the integration of devices from other manufacturers that support OpenVPN
- Allows Weidmüller and compatible third-party devices to be centrally accessed through the same easyConnect environment
- License validity: 1 year

Additional simultaneous VPN connections:

- Available for 1, 5 or 10 additional simultaneous connections
- Increases the number of parallel remote access sessions within the easyConnect instance
- Suitable for additional users or parallel service activities
- License validity: 1 year

U-LINK-EC-10-CONNECTION-1Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Remote access to and from China:
- Dedicated license for devices or service PCs located in China
- Uses the dedicated easyConnect infrastructure provided for China
- License validity: 1 year

Trial license:
A 90-day trial license is available for testing u-link Remote Access in easyConnect. The trial license includes up to 50 devices, up to 50 users and 1 simultaneous VPN connection. The trial license is not available as a separate eShop product and can only be activated directly within easyConnect. The modular licensing concept allows u-link Remote Access in easyConnect to be scaled according to the number of connected devices and required parallel remote access sessions.

通用订货数据

版本	“VPN connection” licence code for u-link Remote Access Service. Can be used as an additional VPN connection or to extend the period of a VPN connection that has already been activated
订货号	3227620000
类型	U-LINK-EC-10-CONNECTION-1Y
数量	ST

数据信息页

U-LINK-EC-10-CONNECTION-1Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

技术数据

尺寸和重量

净重	0 g		

温度

存储温度		工作温度	

功能和特征

额外 VPN 连接的数量 (每个许可证代码)	10 个同步 VPN 接口	VPN 通道带宽	100 Mbit/s
周期	自许可证密钥激活或现有许可证到期之日起 1 年。在激活过程中可以看到单独的许可条款。	用法	作为附加 VPN 通道使用，或延长某个 VPN 通道的期限

系统要求

硬件, 远程目标网络	魏德米勒硬件， 带 u-link VPN 客户端, 带 OpenVPN 客户端的硬件, 带 Docker 客户端的硬件	硬件 (服务计算机)	装有 Windows 10 或 11 操作系统的电脑
门户管理 （用户/设备配置）	通过网络浏览器 (HTTPS), 通过用户名和密码登录	VPN 软件 (服务计算机)	u-link VPN-client (installation on PC)

其他各类

激活	账户管理员在 easyConnect 门户中输入许可证密钥 （功能即刻生效） 。	发货时已含附件	带有许可证密钥的电子邮件

分类

ETIM 8.0	EC000809	ETIM 9.0	EC000809
ETIM 10.0	EC000809	ECLASS 14.0	27-24-25-01
ECLASS 15.0	27-24-25-01		