

QL 2 SAKB10



Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com





The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Cross-connector (terminal), when screwed in, grey, 36 A, Number of poles: 2, Pitch in mm (P): 10.00, Insulated: No, Width: 17 mm
Order No.	<u>0114100000</u>
Туре	QL 2 SAKB10
GTIN (EAN)	4008190056605
Qty.	100 items



QL 2 SAKB10



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals			
ROHS	Conform		
Dimensions and weights			
Depth	2 mm	Depth (inches)	0.0787 inch
Height	6 mm	Height (inches)	0.2362 inch
Width	17 mm	Width (inches)	0.6693 inch
Net weight	1.23 g		
Temperatures			
Storage temperature	-25 °C55 °C	Ambient temperature	-5 °C40 °C
Environmental Product Con	npliance		
RoHS Compliance Status	Compliant without exer	nntion	
REACH SVHC	No SVHC above 0.1 wt ^c	•	
Material data			
Basic material	Cu Zn	Colour	grey
System specifications			3 /
bystem specifications			
Version	Cross-connector		
Additional technical data			
Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	when screwed in
 Dimensions		71 0	
Dillielisiolis			
Pitch in mm (P)	10.00 mm		
General			,
Number of poles	2	Installation advice	Direct mounting
Rating data			'
Nominal current	36 A		
Classifications			
ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40
ECLASS 13.0	27-25-03-03	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		

Creation date 06.11.2025 12:29:44 MEZ

Catalogue status / Drawings 2

QL 2 SAKB10



Weidmüller Interface GmbH & Co. KG

3

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Mounting support



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Туре	BFSC M4X9T	Version
Order No.	0103300000	Mounting screw (Terminal), 4.00 mm, Steel, Depth: 7 mm, Width: 7
GTIN (EAN)	4008190023348	mm, Height: 9 mm
Qty.	100 ST	
Туре	SS M4 D 128-A 4	Version
Type Order No.	SS M4 D 128-A 4 0136400000	Version Lock washer, Copper