Data sheet

IE-KSF-PKV14M-KLROB-25M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables

General ordering data

Order No.	1103660250
Type	IE-KSF-PKV14M-KLROB-25M
GTIN (EAN)	4032248922383
Qty.	1 items

Data sheet

IE-KSF-PKV14M-KLROB-25M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Net weight	3003 g

Temperatures

Storage temperature		Operating temperature	-40 °C...70
Installation temperature			

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

Electrical properties

Operating voltage	30

General standards

Connector standard	IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14

Standards

Connector standard	IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14

Cable structure

Sheathing colour	black (similar to RAL 9005)	Sheath diameter, max.	9.3 mm

Electrical properties of cable

Operating voltage	30

Mechanical and material properties of cable

Min. bending radius, repetitive	10 x cable diameter	Min. bending radius, once only	5 x cable diameter

Classifications

ETIM 8.0	EC001579	ETIM 9.0	EC001579
ETIM 10.0	EC001579	ECLASS 14.0	27-06-05-01
ECLASS 15.0	27-06-05-01		

IE-KSF-PKV14M-KLROB-25M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

