

CLI MH 110 HSTR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections. Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm²
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

General ordering data

Version	CableLine, Accessories, 10 - 317 mm, 110 x 11.3 mm, black
Order No.	0189400000
Type	CLI MH 110 HSTR
GTIN (EAN)	4008190144784
Qty.	100 items

CLI MH 110 HSTR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	3 mm	Depth (inches)	0.1181 inch
Height	110 mm	Height (inches)	4.3307 inch
Width	11.3 mm	Width (inches)	0.4449 inch
Net weight	1.29 g		

Temperatures

Operating temperature range -30...100 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Material colour according to resistance code	0		
Type of printing	neutral		
Version	halogen-free		
Width	11.3 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-30 °C		
Colour	black		
Basic material	Polyamide 66		
Number of markers per packaging unit	Form of supply	Component part	
Recommended industries	Process, Machinery		
Number of markers per combination	1 Component part = Accessories		
Operating temperature range	-30...100 °C		

Conductor and cable markers

Conductor cross-section, max.	500 mm ²	Conductor cross-section, min.	16 mm ²
Conductor O.D., max.	317 mm	Conductor O.D., min.	10 mm
Conductor O.D.	10 - 317 mm	Cross-section for connected wire	16 - 500 mm ²

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

CLI MH 110 HSTR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Example of use

