Data sheet

QL 2 SAKS2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

General ordering data

Version	Cross-connector (terminal), when screwed in, grey, 36 A, Number of poles: 2, Pitch in mm (P): 27.60, Insulated: No, Width: 40.6 mm
Order No.	0207800000
Type	QL 2 SAKS2
GTIN (EAN)	4008190144364
Qty.	20 items
Delivery status	Discontinued
Available until	2024-12-31T00:00:00+01:00

Data sheet

QL 2 SAKS2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	4 mm	Depth (inches)	0.1575 inch
Height	10 mm	Height (inches)	0.3937 inch
Width	40.6 mm	Width (inches)	1.5984 inch
Net weight	11.1 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Copper	Colour	grey

System specifications

Version	for cross-connection link

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No		

Dimensions

Pitch in mm (P)	27.60 mm

General

Number of poles	2	Installation advice	Direct mounting

Rating data

Nominal current	36 A

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		

QL 2 SAKS2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Mounting support



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Type	BFSC M4X9T	Version
Order No.	0103300000	Mounting screw (Terminal), 4.00 mm, Steel, Depth: 7 mm, Width: 7
GTIN (EAN)	4008190023348	mm, Height: 9 mm
Qty.	100 ST	
Type	SS M4 D 128-A 4	Version
Order No.	0136400000	Lock washer, Copper
GTIN (EAN)	4008190118143	
Qty.	100 ST	