


EP 2 SAKG46/32 HP/TF/GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

General ordering data

| | |
|------------|--|
| Version | End and partition plate for terminals, yellow, Height: 160 mm, Width: 2 mm, V-2, PA 66 |
| Order No. | 0205400000 |
| Type | EP 2 SAKG46/32 HP/TF/GE |
| GTIN (EAN) | 4008190027223 |
| Qty. | 10 items |

EP 2 SAKG46/32 HP/TF/GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 90.5 mm | Depth (inches) | 3.563 inch |
| Height | 160 mm | Height (inches) | 6.2992 inch |
| Width | 2 mm | Width (inches) | 0.0787 inch |
| Net weight | 35.7 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|----------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -50 °C...55 °C |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 100 °C |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 8689236b-1c04-4b82-9d8d-177abb5f9950 |

Material data

| | | | |
|---------------------------|-------|--------|--------|
| Basic material | PA 66 | Colour | yellow |
| UL 94 flammability rating | V-2 | | |

System specifications

| | |
|---------|----------------------------|
| Version | End and intermediate plate |
|---------|----------------------------|

Additional technical data

| | |
|---------|----|
| Snap-on | No |
|---------|----|

Dimensions

| | |
|--------------|-------|
| TS 32 offset | 80 mm |
|--------------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000886 | ETIM 9.0 | EC000886 |
| ETIM 10.0 | EC000886 | ECLASS 14.0 | 27-25-03-01 |
| ECLASS 15.0 | 27-25-03-01 | | |