Data sheet

# SCREWTY-M8-DM

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The ideal tool for any application
Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

## General ordering data

| | |
|---|---|
| Version | Cable gland tool for moulded M8 cables |
| Order No. | 1900011000 |
| Type | SCREWTY-M8-DM |
| GTIN (EAN) | 4032248436811 |
| Qty. | 1 items |
| Packaging | Cardboard box |

# SCREWTY-M8-DM

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

| | |
|---|---|
| Net weight | 262 g |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Not affected |
| REACH SVHC | No SVHC above 0.1 wt% |

### Screwing tools

| | | | |
|---|---|---|---|
| Torque setting, max. | 1.7 Nm | Torque setting, min. | 0.5 Nm |

### Important note

| | |
|---|---|
| Product information | Included in delivery:<br>• Torque screwdriver 0.5-1.7 Nm + Setting aid<br>• Interchangeable blade 1/4 inch<br>• Attachment M8 for moulded lines |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC000149 | ETIM 9.0 | EC000149 |
| ETIM 10.0 | EC000149 | ECLASS 14.0 | 21-01-90-90 |
| ECLASS 15.0 | 21-01-90-90 | | |