Data sheet

# CLI C 3-39 SDR SG

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

## General ordering data

| | |
|---|---|
| Version | CableLine, Conductor and cable markers, 8 - 16 mm, 39 x 11 mm, To customer specification |
| Order No. | 1912820000 |
| Type | CLI C 3-39 SDR SG |
| GTIN (EAN) | 4032248542666 |
| Qty. | 100 items |

# CLI C 3-39 SDR SG

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Technical data

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 17 mm | Depth (inches) | 0.6693 inch |
| Height | 39 mm | Height (inches) | 1.5354 inch |
| Width | 11 mm | Width (inches) | 0.4331 inch |
| Net weight | 4.88 g | | |

### Temperatures

| | |
|---|---|
| Operating temperature range | -30...60 °C |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

### General data

| | | | |
|---|---|---|---|
| Orientation of print | horizontal | Type of printing | To customer specification |
| Printing method | Ink jet technology | Version | Loop |
| Width | 11 mm | UL 94 flammability rating | V-0 |
| Operating temperature range, max. | 60 °C | Operating temperature range, min. | -30 °C |
| Colour | To customer specification | Halogen | Yes |
| Basic material | PVC, soft, without Cadmium | Colour of printing | black |
| Printed characters | To customer specification | Operating temperature range | -30...60 °C |
| Imprint | Custom printing | | |

### Conductor and cable markers

| | | | |
|---|---|---|---|
| Halogen | Yes | Conductor cross-section, max. | 70 mm² |
| Conductor cross-section, min. | 16 mm² | Conductor O.D., max. | 16 mm |
| Conductor O.D., min. | 8 mm | Conductor O.D. | 8 - 16 mm |
| Cross-section for connected wire | 16 - 70 mm² | | |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

## CLI C 3-39 SDR SG

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Drawings

Similar to illustration