


NSCH 1M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



With our bus bars in various materials and the associated accessories, you can connect cables in the smallest installation space. Depending on the application, potentials can be collected, distributed or dissipated.

General ordering data

Version	Busbar (terminal), Natural, Height: 15 mm, Depth: 2 mm, Copper
Order No.	0280200000
Type	NSCH 1M
GTIN (EAN)	4008190012953
Qty.	10 M

NSCH 1M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	2 mm	Depth (inches)	0.0787 inch
Height	15 mm	Height (inches)	0.5906 inch
Width	1000 mm	Width (inches)	39.37 inch
Net weight	198.26 g		

Temperatures

Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

Material data

Basic material Copper Surface finish untreated
Colour Natural

Rating data IECEx/ATEX

Certificate No. (IECEX) IECXULD13.0005U Wire cross section max. (IECEX) 2.5 mm²

Additional technical data

Installation advice Direct mounting

Conductors for clamping (rated connection)

Type of connection Screw connection

Dimensions

TS 35 offset 39 mm

General

Installation advice Direct mounting Surface finish untreated

Rating data

Nominal current 24 A

Classifications

ETIM 8.0 EC002848 ETIM 9.0 EC002848
ETIM 10.0 EC002848 ECLASS 14.0 27-14-11-92

Creation date 19.02.2026 03:21:11 MEZ

Catalogue status / Drawings

Technical data

ECLASS 15.0

27-14-11-92

NSCH 1M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Mounting support




We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Type	BFSC M5X8 SCHLITZ	Version	
Order No.	0296700000	Mounting screw (Terminal), 5.00 mm, Steel, Depth: 8.5 mm, Width: 8.5 mm, Height: 8.5 mm	
GTIN (EAN)	4008190881764		
Qty.	100 ST		
Type	DKSUE NSCH/ESCH	Version	
Order No.	0280100000	Fastening element (Terminal), silver, Height: 12.5 mm, Width: 10 mm, Steel, 180 °C	
GTIN (EAN)	4008190036348		
Qty.	100 ST		

Accessories



The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Type	SH 1	Version	
Order No.	0299860000	Busbar support, beige, 100 °C, Width: 26 mm, V-2, Polyamide 66, when screwed in	
GTIN (EAN)	4008190135133		
Qty.	20 ST		