

**AD 3 SAK35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

**General ordering data**

Version	Terminal cover, yellow, PVC, Height: 36 mm, Width: 48 mm, Depth: 1 mm, V-2
Order No.	<a href="#">0273400000</a>
Type	AD 3 SAK35
GTIN (EAN)	4008190106027
Qty.	50 items
Delivery status	This article will no longer be available in the future.
Available until	2026-06-30T00:00:00+02:00

## AD 3 SAK35

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	1 mm	Depth (inches)	0.0394 inch
Height	36 mm	Height (inches)	1.4173 inch
Width	48 mm	Width (inches)	1.8898 inch
Net weight	2.18 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	PVC	Colour	yellow
UL 94 flammability rating	V-2		

### System specifications

Version	End and intermediate plate
---------	----------------------------

### Additional technical data

Snap-on	No	Installation advice	Direct mounting
---------	----	---------------------	-----------------

### General

Installation advice	Direct mounting
---------------------	-----------------

### Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		

## AD 3 SAK35

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

## Accessories

[www.weidmueller.com](http://www.weidmueller.com)

### Mounting support



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

### General ordering data

Type	BFSC M4X32 PA/NA	Version	
Order No.	<a href="#">0129100000</a>	Mounting screw (Terminal), 4.00 mm, Polyamide 66, Depth: 7 mm,	
GTIN (EAN)	4008190020842	Width: 7 mm, Height: 32 mm	
Qty.	100 ST		