

## AD 4 AKZ4

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Product image



Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

### General ordering data

Version	Terminal cover, yellow, PVC, Height: 24.2 mm, Width: 20 mm, Depth: 1 mm, V-2
Order No.	<a href="#">0303400000</a>
Type	AD 4 AKZ4
GTIN (EAN)	4008190068158
Qty.	50 items
Delivery status	This article will no longer be available in the future.
Last order date	2026-06-30T00:00:00+02:00

**AD 4 AKZ4**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	1 mm	Depth (inches)	0.0394 inch
Height	24.2 mm	Height (inches)	0.9528 inch
Width	20 mm	Width (inches)	0.7874 inch
Net weight	0.61 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	PVC	Colour	yellow
UL 94 flammability rating	V-2		

**System specifications**

Version End and intermediate plate

**Additional technical data**

Snap-on	No	Installation advice	Direct mounting
---------	----	---------------------	-----------------

**General**

Installation advice Direct mounting

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		

## AD 4 AKZ4

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Mounting support



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

### General ordering data

Type	BFSC M3X22 PA/RT	Version	
Order No.	<a href="#">0128900000</a>	Mounting screw (Terminal), 3.00 mm, Polyamide 66, Depth: 4.8 mm,	
GTIN (EAN)	4008190084158	Width: 4.8 mm, Height: 22 mm	
Qty.	100 ST		
Type	BFSC M2.5X18 PA/RT	Version	
Order No.	<a href="#">0303300000</a>	Mounting screw (Terminal), 2.50 mm, Polyamide 66, Depth: 3.8 mm,	
GTIN (EAN)	4008190040673	Width: 4.5 mm, Height: 18 mm	
Qty.	100 ST		