

QL 10 SAKD2.5N

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

General ordering data

| | |
|-----------------|--|
| Version | Cross-connector (terminal), when screwed in, grey, 32 A, Number of poles: 10, Pitch in mm (P): 6.00, Insulated: No, Width: 50.3 mm |
| Order No. | 0338000000 |
| Type | QL 10 SAKD2.5N |
| GTIN (EAN) | 4008190164591 |
| Qty. | 20 items |
| Delivery status | This article will no longer be available in the future. |
| Available until | 2026-06-30T00:00:00+02:00 |

QL 10 SAKD2.5N

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 1.5 mm | Depth (inches) | 0.0591 inch |
| Height | 6 mm | Height (inches) | 0.2362 inch |
| Width | 50.3 mm | Width (inches) | 1.9803 inch |
| Net weight | 2.9 g | | |

Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

Environmental Product Compliance

| | | | |
|--------------------------------------|--------------------------------------|--|--|
| RoHS Compliance Status | Compliant with exemption | | |
| RoHS Exemption (if applicable/known) | 6c | | |
| REACH SVHC | Lead 7439-92-1 | | |
| SCIP | 86596b21-b817-43a9-8e4c-ac00e41b9a24 | | |

Material data

Basic material Cu Zn Colour grey

System specifications

Version for cross-connection link

Additional technical data

Type of fixing when screwed in Installation advice Direct mounting
 Explosion-tested version No

Dimensions

Pitch in mm (P) 6.00 mm

General

Number of poles 10 Installation advice Direct mounting

Rating data

Rated voltage 400 V Nominal current 32 A

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ETIM 10.0 | EC000489 | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 | | |

QL 10 SAKD2.5N

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Mounting support



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | KISC M2.5X4.5 WTR2.5 | Version | |
| Order No. | 1062700000 | Mounting screw (Terminal), 2.50 mm, Steel, Depth: 3.8 mm, Width: | |
| GTIN (EAN) | 4008190078454 | 4.5 mm, Height: 4.5 mm | |
| Qty. | 100 ST | | |