

QL 10 SAKS4**Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com

The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Cross-connector (terminal), when screwed in, grey, 47 A, Number of poles: 10, Pitch in mm (P): 10.00, Insulated: No, Width: 226 mm
Order No.	0339000000
Type	QL 10 SAKS4
GTIN (EAN)	4008190025335
Qty.	20 items

QL 10 SAKS4

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

RoHS	Conform
------	---------

Dimensions and weights

Depth	4 mm	Depth (inches)	0.1575 inch
Height	10 mm	Height (inches)	0.3937 inch
Width	226 mm	Width (inches)	8.8976 inch
Net weight	69.74 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Copper	Colour	grey
----------------	--------	--------	------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No		

Dimensions

Pitch in mm (P)	10.00 mm
-----------------	----------

General

Number of poles	10	Installation advice	Direct mounting
-----------------	----	---------------------	-----------------

Rating data

Nominal current	47 A
-----------------	------

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		

QL 10 SAKS4

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Mounting support



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Type	BFSC M4X9T	Version
Order No.	0103300000	Mounting screw (Terminal), 4.00 mm, Steel, Depth: 7 mm, Width: 7
GTIN (EAN)	4008190023348	mm, Height: 9 mm
Qty.	100 ST	
Type	SS M4 D 128-A 4	Version
Order No.	0136400000	Lock washer, Copper
GTIN (EAN)	4008190118143	
Qty.	100 ST	