

KISC M2.5X15/5.5 SAKD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

| | |
|-----------------|--|
| Version | Mounting screw (Terminal), 2.50 mm, Steel, Depth: 3.8 mm, Width: 4.5 mm, Height: 15 mm |
| Order No. | 0367700000 |
| Type | KISC M2.5X15/5.5 SAKD |
| GTIN (EAN) | 4008190170844 |
| Qty. | 100 items |
| Delivery status | This article will no longer be available in the future. |
| Available until | 2026-06-30T00:00:00+02:00 |

KISC M2.5X15/5.5 SAKD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 3.8 mm | Depth (inches) | 0.1496 inch |
| Height | 15 mm | Height (inches) | 0.5906 inch |
| Width | 4.5 mm | Width (inches) | 0.1772 inch |
| Net weight | 0.61 g | | |

Temperatures

| | |
|---------------------|---------------|
| Ambient temperature | -5 °C...40 °C |
|---------------------|---------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|----------------|--------|----------------|---------------|
| Basic material | Steel | Surface finish | Miscellaneous |
| Colour | silver | | |

System specifications

| | |
|---------|-------------|
| Version | for busbars |
|---------|-------------|

Additional technical data

| | | | |
|--------------------------|-----------------|---------------------|-----------------|
| Type of fixing | when screwed in | Installation advice | Direct mounting |
| Explosion-tested version | No | Type of mounting | when screwed in |

Dimensions

| | |
|-------------------------------------|---------|
| Metric size of the thread, external | 2.50 mm |
|-------------------------------------|---------|

General

| | | | |
|---------------------|-----------------|----------------|---------------|
| Installation advice | Direct mounting | Surface finish | Miscellaneous |
|---------------------|-----------------|----------------|---------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002848 | ETIM 9.0 | EC002848 |
| ETIM 10.0 | EC002848 | ECLASS 14.0 | 27-25-03-90 |
| ECLASS 15.0 | 27-25-03-90 | | |