

MB M3/M5 CRM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

| | |
|-----------------|---|
| Version | Sliding nut, M 5 |
| Order No. | 0503500000 |
| Type | MB M3/M5 CRM |
| GTIN (EAN) | 4008 190182083 |
| Qty. | 20 items |
| Delivery status | This article will no longer be available in the future. |
| Available until | 2025-12-31T00:00:00+01:00 |

MB M3/M5 CRM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 14 mm | Depth (inches) | 0.5512 inch |
| Height | 25 mm | Height (inches) | 0.9842 inch |
| Width | 12 mm | Width (inches) | 0.4724 inch |
| Net weight | 3.55 g | | |

Temperatures

| | | | |
|----------------------------------|---------------|----------------------------------|--------|
| Ambient temperature | -5 °C...40 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 100 °C | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------|
| RoHS Compliance Status | Compliant |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|----------------|--------------|---------------------------|-----------|
| Basic material | Polyamide 66 | Surface finish | untreated |
| Colour | Cream | UL 94 flammability rating | V-2 |

System specifications

| | | | |
|---------|------------------------|---------------|-------|
| Version | For the mounting rails | Mounting rail | TS 32 |
|---------|------------------------|---------------|-------|

Additional technical data

| | | | |
|----------------|---------|--------------------------|----|
| Type of fixing | Snap-on | Explosion-tested version | No |
|----------------|---------|--------------------------|----|

Dimensions

| | | | |
|-----------------|-----|-----------------|----------|
| Internal thread | M 5 | Pitch in mm (P) | 12.00 mm |
|-----------------|-----|-----------------|----------|

General

| | | | |
|----------------|-----------|---------------|-------|
| Surface finish | untreated | Mounting rail | TS 32 |
|----------------|-----------|---------------|-------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000096 | ETIM 9.0 | EC000096 |
| ETIM 10.0 | EC000096 | ECLASS 14.0 | 23-11-07-16 |
| ECLASS 15.0 | 23-11-07-16 | | |

MB M3/M5 CRM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

