Data sheet

HTF ZRV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Crimping tools for for turned/stamped contact
- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.

General ordering data

Version	Pressing tool, Crimping tool for contacts, 0.2mm², 1mm², FoderBcrimp
Order No.	9014840000
Type	HTF ZRV
GTIN (EAN)	4008190949969
Qty.	1 items

HTF ZRV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	452.7 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

Technical data

Description of article	Crimping tools for ZRV or MKF flat-blade contacts	Version	Mechanical, without interchangeable inserts

Description of contact

Type of contact	Weidmüller ZRV	Conductor cross-section, max. AWG	AWG 17
Conductor cross-section, min. AWG	AWG 24	Crimping range, max.	1 mm²
Crimping range, min.	0.2 mm²		

tool data crimping

Wire end ferrules cross-section, max.	1 mm²	Wire end ferrules cross-section, min.	0.2 mm²
Crimping type/profile	FoderBcrimp		

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings