


Product image

In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

General ordering data

| | |
|------------|---|
| Version | Cross-connector (terminal), when screwed in, grey, 27 A, Number of poles: 58, Pitch in mm (P): 8.00, Insulated: No, Width: 0.8 mm |
| Order No. | 0545400000 |
| Type | QB 58/8/15 |
| GTIN (EAN) | 4008190028794 |
| Qty. | 10 items |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|----------|-----------------|--------------|
| Depth | 17.5 mm | Depth (inches) | 0.689 inch |
| Height | 458.5 mm | Height (inches) | 18.0511 inch |
| Width | 0.8 mm | Width (inches) | 0.0315 inch |
| Net weight | 21.96 g | | |

Temperatures

| | | | |
|-----------------------|-----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
| Operating temperature | -60 °C...130 °C | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|----------------|--------|--------|------|
| Basic material | Copper | Colour | grey |
|----------------|--------|--------|------|

System specifications

| | |
|---------|---------------------------|
| Version | for cross-connection link |
|---------|---------------------------|

Additional technical data

| | | | |
|--------------------------|-----------------|---------------------|-----------------|
| Type of fixing | when screwed in | Installation advice | Direct mounting |
| Explosion-tested version | No | | |

Dimensions

| | |
|-----------------|---------|
| Pitch in mm (P) | 8.00 mm |
|-----------------|---------|

General

| | | | |
|-----------------|----|---------------------|-----------------|
| Number of poles | 58 | Installation advice | Direct mounting |
|-----------------|----|---------------------|-----------------|

Rating data

| | | | |
|---------------|-------|-----------------|------|
| Rated voltage | 400 V | Nominal current | 27 A |
|---------------|-------|-----------------|------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ETIM 10.0 | EC000489 | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 | | |

Accessories

Disconnect plugs



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

General ordering data

| | | | |
|------------|----------------------------|--------------------------------|--|
| Type | ISPF QB58 SW | Version | |
| Order No. | 0546000000 | Insulation profile, PVC, black | |
| GTIN (EAN) | 4008190116705 | | |
| Qty. | 10 ST | | |

Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

| | | | |
|------------|----------------------------|-------------------------------|--|
| Type | ISPF QB58 RT | Version | |
| Order No. | 0546040000 | Insulation profile, PVC, red | |
| GTIN (EAN) | 4008190497941 | | |
| Qty. | 10 ST | | |
| Type | ISPF QB58 BL | Version | |
| Order No. | 0546080000 | Insulation profile, PVC, blue | |
| GTIN (EAN) | 4008190927035 | | |
| Qty. | 10 ST | | |