Data sheet

STRIPPER PC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm² to 5 x 2.5 mm²
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

General ordering data

Version	Sheathing strippers
Order No.	9918060000
Type	STRIPPER PC
GTIN (EAN)	4032248359172
Qty.	1 items

STRIPPER PC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	25 mm	Depth (inches)	0.9842 inch
Height	35 mm	Height (inches)	1.378 inch
Width	125 mm	Width (inches)	4.9212 inch
Net weight	44.4 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Cable sheathing stripper for data communication lines with 5-15 mm O.D. ø

Stripping tools

Cable type	Data cable / telecommunications and IT	Max. conductor diameter	15 mm
Min. conductor diameter	5 mm	Stripping range AWG, max.	12 AWG
Stripping range AWG, min.	24 AWG	Stripping range, min.	0.25 mm²
Conductor cross-section, max.	4 mm²	Conductor cross-section, min.	0.2 mm²

Classifications

ETIM 8.0	EC000163	ETIM 9.0	EC000163
ETIM 10.0	EC000163	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings